

# Simplese.

Home audio made simple, that's the promise of NuVo's Simplese. Offering four zones and four sources, Simplese delivers the audio experience you want, at a price that's music to your ears.



Keeping things simple is literally what NuVo's Simplese is all about. A perfect fit for just a few rooms of multi-room audio, or expandable to accommodate up to eight different zones, Simplese delivers clean, crisp audio and incredibly straightforward control, affordably.

Use the backlit buttons of the system's keypad to select your source and control the volume, then sit back and enjoy the great sound and great value. Never before has luxury been so easy.

- Direct wiring for clean audio transfer without distortion or interruption
- Music can be shared in four rooms, all playing the same song or different tunes at once
- Four different inputs (CD Player, Satellite, tuner, etc.) allows each person to customize and listen to whatever they want
- High-performance amplifier operates coolly and saves energy
- The easy to use controller installs into the wall offering a low profile way to manage your system
- Using RS-232 protocol, music can be accessed and controlled through a whole home automation system
- A second Simplese® system can add up to four additional rooms of music to accommodate more areas of the home, for a full system of eight zones



# Simplese (NV-A4D).

## Specifications

### Zones 1-4 Power Amplifier Outputs

Continuous Average Output Power	30W (15W x 2)
Two channels driven 30-20kHz @ 1% THD	
Rated Distortion (1/2 Power)	0.40%
Rated Impedance	6 ohm
Damping Factor	50+
Frequency Response	20-20kHz

### Preamplifier Section

Variable Output	0-600mV RMS
Fixed Output	600mV RMS
Impedance	600 ohm

### Source Inputs 1-4

Input Impedance	10K
Input Sensitivity for Rated Power	300mV RMS
Input Overload	3V RMS

### Emitter Outputs

Source Outputs	4
Output Drive Current	100mA
Output Drive Voltage	5VDC
Source 1 and 2	38kHz/56kHz Selectable
Source 3 and 4	38kHz Fixed

### System

System On	5VDC @50mA
External Mute	3-12VDC

### Power Requirements

Power Supply	90-260VAC 50/60Hz
Power Consumption all channels driven to full-rated power	140W
Power Consumption average operating conditions	30W
Power Consumption no signal	Less than 10W

### Regulatory Approvals

CE  
C-Tick  
ETL

### Physical Specifications

Unit Size (mm)	44 H x 430 W x 250 D
Unit Size (inch)	1 3/4 H x 17 W x 10 5/8 D
Shipping Size (mm)	254 H x 508 W x 355.6 D
Shipping Size (inch)	10 H x 20 W x 14 D
Unit Weight (kg)	2.95
Unit Weight (lbs)	6.5
Shipping Weight (kg)	6.80
Shipping Weight (lbs)	15

NuVo reserves the right to change specifications without notice.