

LSA40.

Specifications

Amplifier Outputs

Power	12.5 W x 2 into 8 ohms 1% THD
	20 W x 2 into 4 ohm 1% THD
Distortion at 1kHz (1 Watt)	0.2%
Recommended Impedance	4-8 ohm
Signal to Noise Ratio	75dB, 20Hz- 20kHz

Source Inputs

Input Sensitivity for Full Output	330mV RMS
-----------------------------------	-----------

Regulatory Approvals

CE-EMC
FCC

Physical Specifications

Unit Size with Bezel (mm)	123 H x 78 W x 40 D
Unit Size with Bezel (inch)	4.84 H x 3.07 W x 1.57 D
Unit Size without Bezel (mm)	118 H x 46 W x 40 D
Unit Size without Bezel (inch)	4.64 H x 1.81 W x 1.57 D
Cutout Dimensions (mm)	93 H x 55 W
Cutout Dimensions (inch)	3.66 H x 2.16 W
Shipping Size (mm)	228.6 x 203.2 x 177.79
Shipping Size (inch)	9 x 8 x 7
Unit Weight (kg)	0.12
Unit Weight (lbs)	0.25
Shipping Weight (kg)	0.45
Shipping Weight (lbs)	1.00

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904

Office Direct: 859.817.7200

Email: sales@nuvotechnologies.com

Web: www.nuvotechnologies.com