

Galvanized Steel

Groundrods & Accessories



Bronze Ground Rod Connectors

CATALOGUE #	ROD SIZE	MAX. WIRE SIZE		QTY./PKG.	WT./LBS./C	
729C	5/8"	1/0	Str.Cu.	10	27	
733C	5/8" - 3/4"	3/0	Str.Cu.	50	23	
734C	3/4"	4/0	Str.Cu.	50	36	
710C	1"	250MCM	Str.Cu.	10	100	

CATALOGUE #	SIZE	PKG. QTY.	WT. LBS./C	
	Groundrods (Galv. Steel)			
1205G	1/2" x 5'	10	330	
1206G	1/2" x 6'	10	395	
1207G	1/2" x 7'	10	460	
5806G	5/8" x 6'	10	600	
5807G	5/8" x 7'	5	700	
5808G	5/8" x 8'	5	800	
5810G	5/8" x 10'	5	1000	
3406G	3/4" x 6'	5	900	
3408G	3/4" x 8'	5	1200	
3410G	3/4" x 10'	5	1500	
	Connectors (Galv. Steel)			
725	5/8"-3/4"	10	395	
714R	1/2"	10	460	
	Ground Electrode Inspection Box			
700	10" dia. x 12" deep (H.D. galv.)	5	1200	
724	10" dia. x 24" deep (H.D. galv.)	5	1200	
770	10" dia. x 12" deep (Galv. steel)	5	1200	
	Plastic Ground Wire Moulding & Staples			
701	1/2" plastic moulding x 8 ft.	12	6	
701W	1/2" wood moulding x 8 ft.		6	
702	2" x 1/2" staples x .162"	100	3	
703	2" x 13/16" staples x 3/16"	100	3	
704	3" x 1" staples x 5/16"	100	8	
705	3" x 1 1/2" staples x 1/4"	100	8	
707	1 1/4" x 3/8" staples x 1/4"	500	1	
708	2" x 1 1/16" staples x 3/16"	100	3	
709	3" x 1 1/16" staples x 1/4"	100	3	
	Gradient Control Mat			
6466GCM	6' x 4' Made from 6" x 6" welded mesh 1/4" dia. with pads for installation.	1	29	
6466GCC	6' x 4' 3 only grounding connectors 2/0 AWG 250 MCM	1	30	

POLELINE & GROUNDING