

PROLINE® Frames


PROLINE® Frames


Selection

A full range of sizes for single- and double-bay applications, PROLINE® offers the broadest range of standard sizes in the industry.



Frame Type	Heights mm/in.	Widths mm/in.	Depths mm/in.
Single-Bay Frames	700	600 and 800	600
	1400	600 and 800	500, 600 and 800
	1600	600, 700 and 800	400, 500, 600 and 800
	1800	600, 700, 800 and 1000	400, 500, 600 and 800
	2000	400, 600, 700, 800 and 1000	400, 500, 600 and 800
	2200	600, 700, 800 and 1000	500, 600, 800 and 900
Double-Bay Frames	700	1200	600
	1600	1200	400, 500, 600 and 800
	1800	1200 and 1600	400, 500, 600 and 800
	2000	1200 and 1600	400, 500, 600 and 800
	2200	1200	500, 600 and 800



PROLINE® Frames
Single-Bay Frames

Specifications

- Welded corners with steel corner blocks that add strength and rigidity
- 12 gauge, roll-formed frame sections for strength
- Flange on door and side openings deflect liquids away from the enclosure interior
- Rectangular frame holes are designed for metric cage nut fasteners
- Round frame holes allow numerous grounding locations using M5 thread-forming screws
- Access to both sides of frame mounting holes allows standard components to be easily installed
- Provisions for slide-in subpanel, rack mounting and accessory mounting
- Simple means for joining frames to create multiple-bay enclosures
- An open roll-formed profile design affords complete surface corrosion protection and assembly access
- Sealed mounting for all external accessories
- Finished with RAL 7035 textured gray polyester powder paint


Bulletin: P20
Standard Product

Catalog Number	AxBxC in.	AxBxC mm	Nominal Frame Size A x B x C	Maximum Subpanel Size (mm)	Maximum Subpanel Size (in.)	Maximum Rack Mounting Space
PF766	26.77 x 23.58 x 23.15	680 x 599 x 588	700 x 600 x 600	585 x 530	23.03 x 20.87	13U
PF786	26.77 x 31.46 x 23.15	680 x 799 x 588	700 x 800 x 600	585 x 530	23.03 x 20.87	13U
PF1466	54.33 x 23.58 x 23.15	1380 x 599 x 588	1400 x 600 x 600	1285 x 530	50.59 x 20.87	28U
PF1468	54.33 x 23.58 x 30.20	1380 x 599 x 788	1400 x 600 x 800	1285 x 530	50.59 x 20.87	28U
PF1485	54.33 x 31.46 x 19.21	1380 x 799 x 488	1400 x 800 x 500	1285 x 530	50.59 x 20.87	28U
PF1488	54.33 x 31.46 x 31.02	1380 x 799 x 788	1400 x 800 x 800	1285 x 530	50.59 x 20.87	28U
PF1664	62.20 x 23.58 x 15.28	1580 x 599 x 388	1600 x 600 x 400	1485 x 530	58.46 x 20.87	33U
PF1666	62.20 x 23.58 x 23.15	1580 x 599 x 588	1600 x 600 x 600	1485 x 530	58.46 x 20.87	33U
PF1668	62.20 x 23.58 x 31.02	1580 x 599 x 788	1600 x 600 x 800	1485 x 530	58.46 x 20.87	33U
PF1686	62.20 x 31.46 x 23.15	1580 x 799 x 588	1600 x 800 x 600	1485 x 730	58.46 x 28.74	33U
PF1688	62.20 x 31.46 x 31.02	1580 x 799 x 788	1600 x 800 x 800	1485 x 730	58.46 x 28.74	33U
PF1864	70.08 x 23.58 x 15.28	1780 x 599 x 388	1800 x 600 x 400	1685 x 530	66.34 x 20.87	38U
PF1865	70.08 x 23.58 x 19.21	1780 x 599 x 488	1800 x 600 x 500	1685 x 530	66.34 x 20.87	38U
PF1866	70.08 x 23.58 x 23.15	1780 x 599 x 588	1800 x 600 x 600	1685 x 530	66.34 x 20.87	38U
PF1868	70.08 x 23.58 x 31.02	1780 x 599 x 788	1800 x 600 x 800	1685 x 530	66.34 x 20.87	38U
PF1884	70.08 x 31.46 x 15.28	1780 x 799 x 388	1800 x 800 x 400	1685 x 730	66.34 x 28.74	38U
PF1885	70.08 x 31.46 x 19.21	1780 x 799 x 488	1800 x 800 x 500	1685 x 730	66.34 x 28.74	38U
PF1886	70.08 x 31.46 x 23.15	1780 x 799 x 588	1800 x 800 x 600	1685 x 730	66.34 x 28.74	38U
PF1888	70.08 x 31.46 x 31.02	1780 x 799 x 788	1800 x 800 x 800	1685 x 730	66.34 x 28.74	38U
PF18105	70.08 x 39.33 x 19.21	1780 x 999 x 488	1800 x 1000 x 500	1685 x 930	66.34 x 36.61	38U
PF18106	70.08 x 39.33 x 23.15	1780 x 999 x 588	1800 x 1000 x 600	1685 x 930	66.34 x 36.61	38U
PF18108	70.08 x 39.33 x 31.02	1780 x 999 x 788	1800 x 1000 x 800	1685 x 930	66.34 x 36.61	38U
PF2064	77.95 x 23.58 x 15.28	1980 x 599 x 388	2000 x 600 x 400	1885 x 530	74.21 x 20.87	42U
PF2045	77.95 x 15.28 x 19.21	1980 x 388 x 488	2000 x 400 x 500	1885 x 530	74.21 x 20.87	42U
PF2065	77.95 x 23.58 x 19.21	1980 x 599 x 488	2000 x 600 x 500	1885 x 530	74.21 x 20.87	42U
PF2046	77.95 x 15.28 x 23.15	1980 x 388 x 588	2000 x 400 x 600	1885 x 530	74.21 x 20.87	42U
PF2066	77.95 x 23.58 x 23.15	1980 x 599 x 588	2000 x 600 x 600	1885 x 530	74.21 x 20.87	42U
PF2068	77.95 x 23.58 x 31.02	1980 x 599 x 788	2000 x 600 x 800	1885 x 530	74.21 x 20.87	42U
PF2076	77.95 x 27.52 x 23.15	1980 x 699 x 588	2000 x 700 x 600	1885 x 630	74.21 x 24.80	42U
PF2078	77.95 x 27.52 x 31.02	1980 x 699 x 788	2000 x 700 x 800	1885 x 630	74.21 x 24.80	42U
PF2084	77.95 x 31.46 x 15.28	1980 x 799 x 388	2000 x 800 x 400	1885 x 730	74.21 x 28.74	42U
PF2085	77.95 x 31.46 x 19.21	1980 x 799 x 488	2000 x 800 x 500	1885 x 730	74.21 x 28.74	42U
PF2086	77.95 x 31.46 x 23.15	1980 x 799 x 588	2000 x 800 x 600	1885 x 730	74.21 x 28.74	42U
PF2088	77.95 x 31.46 x 31.02	1980 x 799 x 788	2000 x 800 x 800	1885 x 730	74.21 x 28.74	42U
PF2089	77.95 x 31.46 x 34.96	1980 x 799 x 888	2000 x 800 x 900	1885 x 730	74.21 x 28.74	42U
PF20105	77.95 x 39.33 x 19.21	1980 x 999 x 488	2000 x 1000 x 500	1885 x 930	74.21 x 36.61	42U
PF20106	77.95 x 39.33 x 23.15	1980 x 999 x 588	2000 x 1000 x 600	1885 x 930	74.21 x 36.61	42U
PF20108	77.95 x 39.33 x 31.02	1980 x 999 x 788	2000 x 1000 x 800	1885 x 930	74.21 x 36.61	42U
PF2266	85.83 x 23.58 x 23.15	2180 x 599 x 588	2200 x 600 x 600	2085 x 530	82.09 x 20.87	47U
PF2268	85.83 x 23.58 x 31.02	2180 x 599 x 788	2200 x 600 x 800	2085 x 530	82.09 x 20.87	47U
PF2278	85.83 x 27.52 x 31.02	2180 x 699 x 788	2200 x 700 x 800	2085 x 630	82.09 x 24.80	47U
PF2279	85.83 x 27.52 x 34.96	2180 x 699 x 888	2200 x 700 x 900	2085 x 630	82.09 x 24.80	47U
PF2286	85.83 x 31.46 x 23.15	2180 x 799 x 588	2200 x 800 x 600	2085 x 730	82.09 x 28.74	47U
PF2288	85.83 x 31.46 x 31.02	2180 x 799 x 788	2200 x 800 x 800	2085 x 730	82.09 x 28.74	47U
PF22105	85.83 x 39.33 x 19.21	2180 x 999 x 488	2200 x 1000 x 500	2085 x 930	82.09 x 36.61	47U
PF22106	85.83 x 39.33 x 23.15	2180 x 999 x 588	2200 x 1000 x 600	2085 x 930	82.09 x 36.61	47U

1 rack unit = 1.75 in. (44 mm)



PROLINE® Frames



87414905



PROLINE® Frames

Notes