




Wallplates and Face Plates

Nylon and Metal Wallplates

	Description	Color	Toggle Switch Plates		Duplex Receptacle Plates		GFCI, Surge & Style Line® Receptacle Plates	
			1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang
 NP1AL	Standard, Smooth High-Impact Nylon.	Almond	NP1AL	NP2AL	NP8AL	NP82AL	NP26AL	NP262AL
		Ivory	NP1I	NP2I	NP8I	NP82I	NP26I	NP262I
		White	NP1W	NP2W	NP8W	NP82W	NP26W	NP262W
		Brown	NP1	NP2	NP8	NP82	NP26	NP262
		Gray	NP1GY	NP2GY	NP8GY	NP82GY	NP26GY	NP262GY
		Office White	NP1OW	NP2OW	NP8OW	NP82OW	NP26OW	NP262OW
		Black	NP1BK	NP2BK	NP8BK	NP82BK	NP26BK	NP262BK
		Red	NP1R	NP2R	NP8R	NP82R	NP26R	NP262R
		Orange	—	—	NP8OR	NP82OR	—	—
		 NP8AL	Plated Steel.	Chrome	SCH1	SCH2	SCH8	SCH82
Brass	SBP1			SBP2	SBP8	SBP82	SBP26	SBP262
 NP26AL	Stainless Steel.	Smooth	SS1	SS2	SS8	SS82	SS26	SS262
		Beveled	97071	—	97101	—	—	—
	Brass.	Smooth	SB1	SB2	SB8	SB82	SB26	SB262
		Smooth	SA1	SA2	SA8	SA82	—	—
	Anodized Aluminum.	Smooth	SA1	SA2	SA8	SA82	—	—

Duplex and Style Line® Plates











IFP18AL














IFP126AL

Description	Color	Catalog Numbers
Duplex Plate with label fields. (Accepts Duplex Frames)	Almond	IFP18AL
	Gray	IFP18GY
	Office White	IFP18OW
Style Line® Plate with label fields. (Accepts Style Line Frames)	Almond	IFP126AL
	Gray	IFP126GY
	Office White	IFP126OW

IFP Face Plates

Color	1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 6-Port	9-Port	12-Port
								
Almond	IFP11AL	IFP12AL	IFP13AL	IFP14AL	IFP16AL	IFP26AL	IFP29AL	IFP212AL
Gray	IFP11GY	IFP12GY	IFP13GY	IFP14GY	IFP16GY	IFP26GY	IFP29GY	IFP212GY
Office White	IFP11OW	IFP12OW	IFP13OW	IFP14OW	IFP16OW	IFP26OW	IFP29OW	IFP212OW
Black	IFP11BK	IFP12BK	IFP13BK	IFP14BK	IFP16BK	IFP26BK	IFP29BK	IFP212BK
Electric Ivory	IFP11EI	IFP12EI	IFP13EI	IFP14EI	IFP16EI	IFP26EI	IFP29EI	IFP212EI
White	IFP11W	IFP12W	IFP13W	IFP14W	IFP16W	IFP26W	IFP29W	IFP212W

SSF Stainless Steel Plates

1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 4-Port	6-Port	9-Port	12-Port
								
SSF11	SSF12	SSF13	SSF14	SSF16	SSF204	SSF206	SSF209	SSF212
With Label Fields						Keystone Opening Hole size for mounting all Hubbell Jacks B  A: .580" (14.73) B: .760" (19.30)		
1-Port	2-Port	3-Port	4-Port	6-Port				
SSFL11	SSFL12	SSFL13	SSFL14	SSFL16				

Note: All SSF plates will accept Audio/Video keystone connectors and Xcelerator™ jacks.







iSTATION™ and Outlet Frames

IMF iSTATION™ Frames





The IMF series accepts iSTATION™ modules in 3 unit combinations for 1-gang and 6 unit combinations for 2-gang applications. Start by selecting a frame and then the required mix of modules. See pages 166 and 167 for module combinations.

Color	1-Gang		2-Gang	
Almond	IMF1AL		IMF2AL	
Black	IMF1BK		IMF2BK	
Electric Ivory	IMF1EI		IMF2EI	
Gray	IMF1GY		IMF2GY	
Office White	IMF1OW		IMF2OW	
White	IMF1W		IMF2W	

Style Line® Outlet Frames, Unloaded

	2-Port	3-Port	4-Port	6-Port
				
Color	Catalog Numbers			
Almond	ISF2AL	ISF3AL	ISF4AL	ISF6AL
Black	ISF2BK	ISF3BK	ISF4BK	ISF6BK
Electric Ivory	ISF2EI	ISF3EI	ISF4EI	ISF6EI
Gray	ISF2GY	ISF3GY	ISF4GY	ISF6GY
Office White	ISF2OW	ISF3OW	ISF4OW	ISF6OW
White	ISF2W	ISF3W	ISF4W	ISF6W

Style Line® Outlet Frames, Loaded

	15-Pin 3.5mm Jack	15-Pin XLR	15-Pin D-sub F/F Gender Changer	15-Pin D-sub Screw Terminal
				
Color	Catalog Numbers			
Almond	ISF1535AL	ISFXLRAL	ISFD15AL	ISFD15STAL
Black	ISF1535BK	ISFXLRBK	ISFD15BK	ISFD15STBK
Electric Ivory	ISF1535EI	ISFXLREI	ISFD15EI	ISFD15STEI
Gray	ISF1535GY	ISFXLRGY	ISFD15GY	ISFD15STGY
Office White	ISF1535OW	ISFXLRW	ISFD15OW	ISFD15STOW
White	ISF1535W	ISFXLRW	ISFD15W	ISFD15STW

Outlet Frames

	Duplex 2-Port	Duplex 4-Port	Style Line Loaded 4-Port T568B	Style Line Loaded 4-Port T568A
				
Color	Catalog Numbers			
Almond	BR106AL	Q106AL	—	—
Black	BR106B	Q106B	SL5E4B*	SL5E4A*
Electric Ivory	BR106E	Q106E	—	—
Gray	BR106G	Q106G	—	—
Office White	BR106C	Q106O	—	—
White	BR106W	Q106W	—	—

Note: * SL5E4A and SL5E4B have four Category 5e jacks built into the frame.

Snap Fit Connector Fittings



SFRC110R



SFRCR



SFRCRFF



SFSV110BK



SFSVBK



SFBGY



SFFBX



SFRFGOW



SFB10

RCA Connectors

Use to distribute component and composite audio and video signals from device to device. Typical applications include TV, cable, VCR/DVD, camera, camcorder, projector, home theater, and entertainment centers.

110 Punchdown

Insulator Color	Red	White	Yellow	Blue	Green
Black Housing.	SFRC110R	SFRC110W	SFRC110Y	SFRC110B	SFRC110GN

Solder Coupler Termination

Insulator Color	Black	Red	White	Yellow	Blue	Green
Office White Housing.	SFRC	SFRCR	SFRCW	SFRCY	SFRCBOW	SFRCGNOW
Other Color Housing.	SFRC*	SFRCR*	SFRCW*	SFRCY*	SFRCB*	SFRCGN*

Gold Pass-through, F/F Coupler

Insulator Color	Black	Red	White	Yellow	Blue	Green
Office White Housing.	SFRCBKFF	SFRCRFF	SFRCWFF	SFRCYFF	SFRCBFFOW	SFRCGNFFOW
Other Color Housing.	SFRCBKFF*	SFRCRFF*	SFRCWFF*	SFRCYFF*	SFRCBFF*	SFRCGNFF*

Note: * For other housing colors, add "AL" (Almond), "BK" (Black), "EI" (Electric Ivory), "GY" (Gray) or "W" (White) to the end of the catalog number.

S-Video Connectors

Use to transmit video information over a cable by dividing the signal into two separate signals, (chrominance) for color and (luminance) for brightness. Applications include TV, cable, satellite, VCR/DVD, camera, camcorder, projector, home theater, entertainment systems, security and surveillance.

Termination	Almond	Black	Electric Ivory	Gray	Office White	White
110	SFSV110AL	SFSV110BK	SFSV110EI	SFSV110GY	SFSV110OW	SFSV110W
F/F Coupler	SFSVAL	SFSVBK	SFSVEI	SFSVGY	SFSVOW	SFSVW

BNC Connectors

Use to distribute PRO audio/video through coaxial 75 ohm signal to the work area. Applications include TV, CCTV, analog and digital CATV, VCR, HDTV satellite, security and surveillance systems.

Finish	Almond	Black	Electric Ivory	Gray	Office White	White
Nickel	SFBAL	SFBBK	SFBEI	SFBGY	SFBOW	SFBW
Gold	SFBGAL	SFBGBK	SFBGEI	SFBGGY	SFBGOW	SFBGW

F-Type Connectors

Use for distributing high quality video signal to the workstation. Requiring no soldering, these F-connectors install with a snap and provide quick, easy "screw-on" termination. Applications include TV, CCTV and CATV, home theater and entertainment systems, satellite, security and surveillance systems, VCR/DVD applications.

F-Type Coupler Bulkhead F/F

Finish	Almond	Black	Electric Ivory	Gray	Office White	White
Nickel	SFFALX	SFFBX	SFFEX	SFFGX	SFFX	SFFWX
Gold	SFFGAL	SFFGBK	SFFGEI	SFFGGY	SFFGOW	SFFGW

F-Type to RCA Bulkhead F/F

Finish	Office White	White
Gold	SFRFGOW	SFRFGW

Blank Connectors

Sold 10 pieces per package.

Color	Almond	Black	Electric Ivory	Gray	Office White	White
Housing Color	SFBAL10	SFB10	SFBE10	SFBG10	SFB10	SFBW10

Snap Fit Connector Fittings

Gold Speaker Post Connectors and Plugs

Use for distributing audio signal throughout the home, office or to a workstation. Applications include home theater, surround sound systems, entertainment systems, and speaker connections.

Speaker Post Connectors

Ring Color	Housing Color	Catalog Numbers
Black	Office White	SFSPGBK
Red	Office White	SFSPGR

Speaker Post Plugs

Sold 10 pieces per package.

Color	Catalog Numbers
Black	SPPBK10
Red	SPPR10



SFSPGR



SPPBK10

3.5mm Stereo Jacks

Use for distributing stereo or mono audio signals to and from devices. Applications include laptop and desktop computer audio I/O output, Pro audio distribution, projectors, and IR (infrared) signal transmission.

Size	Almond	Black	Electric Ivory	Gray	Office White	White
3.5mm	SF35SJAL	SF35SJBK	SF35SJEI	SF35SJGY	SF35SJ	SF35SJW



SF35SJ

USB Connectors

Use to provide a simple and easy way to add a USB 2.0 connection to a work area. Feed-through coupler A-to-A or A-to-B format options available.

Color	Format	Catalog Number
Blue	A-to-B	SFUSBABB
Red	A-to-A	SFUSBAAB



SFUSBABB

ST Keystone Fiber Adapter

Color	Almond	Black	Electric Ivory	Gray	Office White	White
	SFSTAL	SFSTBK	SFSTEI	SFSTG	SFST	SFSTW



SFST

Category 6 Jacks

The XJ6 jack supports 10GbE applications to 55 meters, Gigabit Ethernet in the backbone, and network convergence out to the work area with usable bandwidth of 500 MHz. Sold 1 per bag, carton of 25.

Color	Catalog Numbers	Color	Catalog Numbers	Color	Catalog Numbers
Almond	HXJ6AL	Gray	HXJ6GY	Red	HXJ6R
Black	HXJ6BK	Green	HXJ6GN	White	HXJ6W
Blue	HXJ6B	Office White	HXJ6OW	Yellow	HXJ6Y
Electric Ivory	HXJ6EI	Orange	HXJ6OR		



HXJ6GN

Category 5e Jacks

The XJ5e jack supports 10/100/1000BASE-T applications with usable bandwidth of 190 MHz in the channel. Sold 1 per bag, carton of 25.

Color	Catalog Numbers	Color	Catalog Numbers	Color	Catalog Numbers
Almond	HXJ5EAL	Gray	HXJ5EGY	Red	HXJ5ER
Black	HXJ5EBK	Green	HXJ5EGN	White	HXJ5EW
Blue	HXJ5EB	Office White	HXJ5EOW	Yellow	HXJ5EY
Electric Ivory	HXJ5EEI	Orange	HXJ5EOR		



HXJ5EBK

6 Position USOC Jacks

The XJU jack supports all low-speed data and voice grade applications. Sold 1 per bag, carton of 25.

Color	Catalog Numbers	Color	Catalog Numbers	Color	Catalog Numbers
Almond	HXJUJAL	Gray	HXJUGY	Red	HXJUR
Black	HXJUBK	Green	HXJUGN	White	HXJUW
Blue	HXJUB	Office White	HXJUOW	Yellow	HXJUJY
Electric Ivory	HXJUEI	Orange	HXJUOR		



HXJUOW

Keystone Opening

Hole size for mounting all Hubbell jacks and connectors.



A: .580" (14.73)
B: .760" (19.30)

iSTATION™ Audio/Video Modules

15-Pin and 9-Pin

Hubbell's expanded line of 15-pin VGA-style connectors are supplied in various iSTATION™ module styles to accommodate the industry's growing needs for expansion. Hubbell's 9-pin high-density D-sub modules allow easy access to RS232 control and serial devices. Applications include video distribution, desktop and laptop computers, monitors, cameras and projectors, home theater and entertainment.

	15-Pin F/F Gender Changer 1 Unit	15-Pin F/Screw Terminal, SVGA 1 Unit	15-Pin VGA 3.5mm Stereo Jack 1.5 Unit	9-Pin F/F Gender Changer 1 Unit	15-Pin Blank 10-pack 1 Unit
					
Color Office White	IM15DIN1OW*	IM15ST1OW*	IM15315OW*	IM9DIN1OW*	IMBDS1OW*

Note: * For other colors, replace "OW" with: "AL" (Almond), "GY" (Gray), "BK" (Black), "EI" (Electric Ivory) or "W" (White).

Note: Order **IMBDS1** series blank modules with D-sub connectors for iSTATION™ applications.











	15-Pin to 6-Pin DIN Whip 10-pack	15-Pin Crimp On 10-pack	15-Pin Screw Terminal 10-pack	15-Pin Gender Changer 10-pack
				
Catalog Numbers	156P10	15C10	15ST10	15GC10

	DVI F/F Gender Changer 1.5 Unit	DVI to 15-Pin 1.5 Unit
		
Color Office White	IMDVI15OW*	IM15DVI15OW*

Note: * For other colors, replace "OW" with: "AL" (Almond), "GY" (Gray), "BK" (Black), "EI" (Electric Ivory) or "W" (White).

Audio/Video Modules

Hubbell's wide offering of iSTATION™ loaded and unloaded modules is the most extensive Audio/Video solution in the structured cabling industry. Whatever the specification, application or preference, Hubbell iSTATION™ modules answers the call. Applications include Audio/video distribution devices, desktop and laptop computers, cameras and projectors, home theater and entertainment systems. All modules are 1 unit except **IMCRS15** series (1.5 unit).

	RCA Component A/V 5 RCAs, Solder 1.5 Unit	RCA Component 3 RCAs, Solder	RCA Component 3 RCAs, Feed-Thru F/F	RCA Audio 2 RCAs, 110 UTP	S-Video 2 RCAs, 110 UTP	Speaker Post
						
Color Office White	IMCRS15OW*	IMCRS1OW*	IMCRF1OW*	IMAR1101OW*	IMSR1101OW*	IMSP1OW*
Catalog Number						
	S-Video, 3.5mm Composite 110 UTP	3 RCA Component 110 UTP	3 RCA 110 UTP	RCA A/V Solder-Type	RCA A/V Gold F/F Feed-Thru	RCA 3.5mm Solder
						
Color Office White	IMSV351101OW*	IMR1101OW*	IMCR1101OW*	IM3RS1OW*	IM3RF1OW*	IMRSJ1OW*
Catalog Numbers						

Note: * For other colors, replace "OW" with: "AL" (Almond), "GY" (Gray), "BK" (Black), "EI" (Electric Ivory) or "W" (White).

iSTATION™ Audio/Video Modules

XLR, Speakon® and ¼" Modules

Applications include Video distribution, desktop and laptop computers, monitors, cameras, microphones and projectors, home theater and entertainment. Note: Order **IMAVB15** Series blank modules with AV connectors for iSTATION™ applications.






	AV Blank 1.5 Unit 10-pack	XLR Screw Terminal 10-pack	XLR Solder-Type 10-pack	¼" Stereo Jack Solder-Type 10-pack	Speakon® Conn. Solder-Type 10-pack	USB Feed-Thru A-to-B 10-pack
						
Color	Office White					
Catalog Numbers	IMAVB15OW*	XLRST10	XLR10	14S10	SC10	USB10

Note: * For other colors, replace "OW" with: "AL" (Almond), "GY" (Gray), "BK" (Black), "EI" (Electric Ivory) or "W" (White).

Unloaded Modules

Applications include Video distribution, desktop and laptop computers, monitors, cameras and projectors, home theater and entertainment.

	Keystone 1-Port, Flat 1 Unit	Keystone 2-Port, Flat 1 Unit	Keystone 1-Port, Angled 1.5 Unit	Keystone 2-Port, Angled 1.5 Unit	SC Angled 1 Duplex 1.5 Unit	SC Angled 2 Duplex 2 Unit
						
Color	Catalog Numbers					
Almond	IM1K1AL	IM2K1AL	IM1KA15AL	IM2KA15AL	IM1SCA15AL	IM2SCA2AL
Black	IM1K1BK	IM2K1BK	IM1KA15BK	IM2KA15BK	IM1SCA15BK	IM2SCA2BK
Electric Ivory	IM1K1EI	IM2K1EI	IM1KA15EI	IM2KA15EI	IM1SCA15EI	IM2SCA2EI
Gray	IM1K1GY	IM2K1GY	IM1KA15GY	IM2KA15GY	IM1SCA15GY	IM2SCA2GY
Office White	IM1K1OW	IM2K1OW	IM1KA15OW	IM2KA15OW	IM1SCA15OW	IM2SCA2OW
White	IM1K1W	IM2K1W	IM1KA15W	IM2KA15W	IM1SCA15W	IM2SCA2W

	Blank 0.5 Unit	Blank 1 Unit	Blank 1.5 Unit	Keystone Recessed Angle 1-Port, 1.5 Unit	Keystone Recessed Angle 2-Port, 1.5 Unit
					
Color	Catalog Numbers				
Almond	IMB05AL	IMB1AL	IMB15AL	IM1IA15AL	IM2IA15AL
Black	IMB05BK	IMB1BK	IMB15BK	-	-
Electric Ivory	IMB05EI	IMB1EI	IMB15EI	-	-
Gray	IMB05GY	IMB1GY	IMB15GY	IM1IA15GY	IM2IA15GY
Office White	IMB05OW	IMB1OW	IMB15OW	IM1IA15OW	IM2IA15OW
White	IMB05W	IMB1W	IMB15W	-	-

IMF iSTATION™ Frames

The IMF series accepts iSTATION™ modules in 3 unit combinations for 1-gang and 6 unit combinations for 2-gang applications. Start by selecting a frame and then the required mix of modules.

Color	1-Gang	2-Gang
Almond	IMF1AL	IMF2AL
Black	IMF1BK	IMF2BK
Electric Ivory	IMF1EI	IMF2EI
Gray	IMF1GY	IMF2GY
Office White	IMF1OW	IMF2OW
White	IMF1W	IMF2W

Speakon® is a registered trademark of Neutrik.