

### Hubbell Xcelerator Jacks, Category 6

The NEXTSPEED® Category 6 system is designed to deliver headroom beyond 500MHz for dependable Multi-gigabit Ethernet applications. NEXTSPEED's extended bandwidth provides reliability with zero bit error rate performance for today's high speed digital communications.



HXJ6B



HXJ6OR

Color	Catalog Number	Bag of 25 Catalog Number
Almond	HXJ6AL	HXJ6AL25
Black	HXJ6BK	HXJ6BK25
Blue	HXJ6B	HXJ6B25
Gray	HXJ6GY	HXJ6GY25
Green	HXJ6GN	HXJ6GN25
Ivory	HXJ6EI	HXJ6EI25
Light Almond	HXJ6LA	HXJ6LA25
Office White	HXJ6OW	HXJ6OW25
Orange	HXJ6OR	HXJ6OR25
Red	HXJ6R	HXJ6R25
White	HXJ6W	HXJ6W25
Yellow	HXJ6Y	HXJ6Y25

### Hubbell Xcelerator Jacks, Category 5e

Supports 10/100/1000BASE-T applications with usable bandwidth of 190 MHz in the channel.



HXJ5EBK

Color	Catalog Number	Bag of 25 Catalog Number
Almond	HXJ5EAL	HXJ5EAL25
Black	HXJ5EBK	HXJ5EBK25
Blue	HXJ5EB	HXJ5EB25
Gray	HXJ5EGY	HXJ5EGY25
Green	HXJ5EGN	HXJ5EGN25
Ivory	HXJ5EEI	HXJ5EEI25
Light Almond	HXJ5ELA	HXJ5ELA25
Office White	HXJ5EOW	HXJ5EOW25
Orange	HXJ5EOR	HXJ5EOR25
Red	HXJ5ER	HXJ5ER25
White	HXJ5EW	HXJ5EW25
Yellow	HXJ5EY	HXJ5EY25

### Hubbell Xcelerator Jacks, 6-Position USOC



HXJUEI

Color	Catalog Number	Bag of 25 Catalog Number
Almond	HXJUAL	-
Black	HXJUBK	-
Blue	HXJUB	-
Gray	HXJUGY	-
Green	HXJUGN	-
Ivory	HXJUEI	-
Light Almond	HXJULA	-
Office White	HXJUOW	HXJUOW25
Orange	HXJUOR	-
Red	HXJUR	-
White	HXJUW	-
Yellow	HXJUY	-

### Jack Icons\*

Bag of 100 icons. Snaps to front of enterprise grade Hubbell Xcelerator jacks.



IP100C

Color	Blank	Computer	Telephone
Black	IBK100	IBK100C	IBK100T
Blue	IB100	IB100C	IB100T
Brown	IBN100	IBN100C	IBN100T
Gray	IGY100	IGY100C	IGY100T
Green	IGN100	IGN100C	IGN100T
Ivory	IEI100	IEI100C	IEI100T
Orange	IOR100	IOR100C	IOR100T
Purple	IP100	IP100C	IP100T
Red	IR100	IR100C	IR100T
White	IW100	IW100C	IW100T
Yellow	IY100	IY100C	IY100T

Note: \*Not UL Listed, CSA Certified.

### F-Type Connectors

Distributes high quality video signal to the workstation. These connectors install with a snap and provide quick, easy “screw-on” termination. Compatible with TV, CATV and CCTV, home theater and entertainment systems, satellite, security and surveillance systems, VCR/DVD applications.

Color	F-Type Coupler Bulkhead F/F	F-Type Coupler Bulkhead F/F Gold	F-Type to RCA Bulkhead F/F Gold	F-Type Recessed
Almond	<b>SFFALX</b>	<b>SFFGAL</b>	–	–
Black	<b>SFFBX</b>	<b>SFFGBK</b>	<b>SFRFGBK</b>	<b>SFGRFBK</b>
Gray	<b>SFFGX</b>	<b>SFFGGY</b>	<b>SFRFGGY</b>	<b>SFGRFGY</b>
Ivory	<b>SFFEX</b>	<b>SFFGEI</b>	<b>SFRFGEI</b>	<b>SFGRFEI</b>
Light Almond	<b>SFFLAX</b>	<b>SFFGLA</b>	–	–
Office White	<b>SFFX</b>	<b>SFFGOW</b>	<b>SFRFGOW</b>	<b>SFGRFOW</b>
White	<b>SFFWX</b>	<b>SFFGW</b>	<b>SFRFGW</b>	<b>SFGRFW</b>



**SFFGGY**



**SFGRFOW**



**SFR110R**



**SFRRCR**



**SFRRCROW**



**SFRRCRF**



**SFSV110BK**

### RCA Connectors

Distributes component and composite audio and video signals from device to device. Typical applications include TV, cable, VCR/DVD, camera, camcorder, projector, home theater, and entertainment centers.

Insulator Color	RCA 110 Punch-Down Black Housing	RCA Solder Coupler Termination		
		Office White Housing	Additional Housing Color*	RCA Recessed*
Black	–	<b>SFRC</b>	<b>SFRCBKxx</b>	<b>SFRCBKRxx</b>
Blue	<b>SFRC110B</b>	<b>SFRCBOW</b>	<b>SFRCBxx</b>	<b>SFRCBRxx</b>
Green	<b>SFRC110GN</b>	<b>SFRCGNOW</b>	<b>SFRCGNxx</b>	<b>SFRCGNRxx</b>
Orange	–	<b>SFRCOROW</b>	<b>SFRCORxx</b>	<b>SFRCORRxx</b>
Red	<b>SFRC110R</b>	<b>SFRCR</b>	<b>SFRCRxx</b>	<b>SFRCRRxx</b>
White	<b>SFRC110W</b>	<b>SFRCW</b>	<b>SFRCWxx</b>	<b>SFRCWRxx</b>
Yellow	<b>SFRC110Y</b>	<b>SFRCY</b>	<b>SFRCYxx</b>	<b>SFRCYRxx</b>

Insulator Color	RCA Gold Pass-through, Office White Housing	F/F Coupler Additional Housing Color*
Black	<b>SFRCBKFF</b>	<b>SFRCBKFFxx</b>
Blue	<b>SFRCBFFOW</b>	<b>SFRCBFFxx</b>
Green	<b>SFRCGNFFOW</b>	<b>SFRCGNFFxx</b>
Orange	<b>SFRCORFFOW</b>	<b>SFRCORFFxx</b>
Red	<b>SFRCRFF</b>	<b>SFRCRFFxx</b>
White	<b>SFRCWFF</b>	<b>SFRCWFFxx</b>
Yellow	<b>SFRCYFF</b>	<b>SFRCYFFxx</b>

Note: \*Additional Housing colors: **xx** = **AL** (Almond), **BK** (Black), **EI** (Ivory), **GY** (Gray), **LA** (Light Almond), and **W** (White).

### S-Video Connectors

Transmits video information over a cable by dividing the signal into two separate signals (chrominance) for color and (luminance) for brightness. Applications include cable, satellite, DVD, camera, camcorder, projector, home theater, entertainment systems, security, and surveillance.

Color	S-Video 110 Punch-Down	S-Video F/F Coupler
Black	<b>SFSV110BK</b>	<b>SFSVBK</b>



#### Gender Changers, 9 and 15-Pin Connections

Unit of Measure	15-Pin, 90° F/F Coupler	HD 9-Pin F/F Coupler	HD 15-Pin F/F Coupler
1 per bag	<b>15901</b>	–	–
10 per bag	<b>159010</b>	<b>9GC10</b>	<b>15GC10</b>

#### Screw Terminal, 9 and 15-Pin Connections

Unit of Measure	HD 9-Pin Screw Term	HD 15-Pin Screw Term	HD 15-Pin, Screw Term, Keystone Front Mount
10 per bag	<b>9ST10</b>	<b>15ST10</b>	<b>SF15ST</b>



SFBBOW



SFBGOW



SFSPGR



SPPBK10



SF35FFOW



SF35STOW



SFC5EW



SFC6EBK



SFUSBAA3BK



SFUSBAB3BK



SFUSBABB



SFUSBAAB



SFB10



SFSBEI10

### BNC Connectors

Distributes PRO audio video through coaxial 75 ohm signal to the work area. Applications include TV, CCTV, analog and digital CATV, VCR, HDTV satellite, security and surveillance systems.

Color	BNC Connector Nickel Finish	BNC Connector Gold Finish
Black	<b>SFBBK</b>	<b>SFBGBK</b>
Gray	<b>SFBGY</b>	<b>SFBGGY</b>
Ivory	<b>SFBEI</b>	<b>SFBGEI</b>
Light Almond	<b>SFBLA</b>	<b>SFBGLA</b>
Office White	<b>SFBOW</b>	<b>SFBGOW</b>
White	<b>SFBW</b>	<b>SFBGW</b>

### Gold Speaker Post Connectors and Plugs\*

Ring Color	Speaker Post Connector Office White Housing	Speaker Post/ Banana Plugs
Black	<b>SFSPGBK</b>	<b>SPPBK10</b>
Red	<b>SFSPGR</b>	<b>SPPR10</b>

### 3.5mm Stereo Jacks\*

Distributes stereo or mono audio signals to and from devices. Applications include laptop and desktop computer audio I/O output, PRO audio distribution, projectors, and IR (infrared) signal transmission.

Housing Color	3.5mm F/F Coupler	3.5mm Stereo Jack	3.5mm Screw Term.
Black	<b>SF35FFBK</b>	<b>SF35SJBK</b>	<b>SF35STBK</b>
Gray	<b>SF35FFGY</b>	<b>SF35SJGY</b>	<b>SF35STGY</b>
Ivory	<b>SF35FFEI</b>	<b>SF35SJEI</b>	<b>SF35STEI</b>
Light Almond	<b>SF35FFLA</b>	<b>SF35SJLA</b>	<b>SF35STLA</b>
Office White	<b>SF35FFOW</b>	<b>SF35SJ</b>	<b>SF35STOW</b>
White	<b>SF35FFW</b>	<b>SF35SJW</b>	<b>SF35STW</b>

### Inline Couplers\*

Use to deliver a quick and easy interconnect solution at the desktop or in the cross connect.

Color	Wiring: T568A/B	Wiring: T568A/B
Black	<b>SFC5EBK</b>	<b>SFC6EBK</b>
White	<b>SFC5EW</b>	<b>SFC6EW</b>

### USB Connectors

Use to provide a simple and easy way to add a USB connection to a work area.

Housing Color	USB 3.0, A to A, Pass-Thru, F/F, Coupler	USB 3.0, A to B, Pass-Thru, F/F, Coupler	USB 2.0, A to A, Pass-Thru, F/F, Coupler	USB 2.0, A to B, Pass-Thru, F/F, Coupler
Black	<b>SFUSBAA3BK</b>	<b>SFUSBAB3BK</b>	-	-
Blue	-	-	<b>SFUSBAAB</b>	<b>SFUSBABB</b>
Office White	-	-	<b>SFUSBAAOW</b>	<b>SFUSBABOW</b>
White	-	-	<b>SFUSBAAW</b>	<b>SFUSBABW</b>

### Blank Connectors, 10-Pack

Housing Color	Blanks	Smooth Blanks
Almond	<b>SFBAL10</b>	<b>SFSBAL10</b>
Black	<b>SFB10</b>	<b>SFSBBK10</b>
Gray	<b>SFBG10</b>	<b>SFSBGY10</b>
Ivory	<b>SFBE10</b>	<b>SFSBEI10</b>
Light Almond	<b>SFBLA10</b>	<b>SFSBLA10</b>
Office White	<b>SFB10</b>	<b>SFSBOW10</b>
White	<b>SFBW10</b>	<b>SFSBW10</b>

Note: \*Not UL Listed.