

## PARTIAL SWING-OUT RACK FRAME



This 19-in. Rack Frame is used when a smaller, medium-duty swing-out frame is desired. Light-weight rack equipment fits nicely into this 800-mm tall swing-out frame providing 90 degrees of rotation and increased accessibility.

- Side hinge brackets are used to mount the swing frame, allowing free access above and below the swing frame
- Used with any height enclosure and hinged on the right or left
  Maximum equipment lead is 100 lb
- Maximum equipment load is 100 lb.
- Furnished with hinges, two quarter-turn latches and mounting hardware
- RAL 7035 textured gray finish
- Complies with ANSI/EIA RS-310-D rack mounting standards

## HEAVY-DUTY SWING-OUT RACK FRAME


- Allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Hinges that provide 170-degree rotation are optional.
- Spring-loaded pivot post makes installation easy
- Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames
- Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.
- Mounting supports can be assembled to the top and bottom of the frame for full-height rack-mounting frames. Smaller rack-mounting frames can be mounted to the vertical frame members or to the grid straps. Order separately.
- Furnished with hinges, two quarter-turn latches and mounting hardware RAL 7035 textured gray finish
- Complies with ANSI/EIA RS-310-D rack-mounting standards
- Maximum equipment load is 300 lb.
- Mounting holes accommodate either English or metric cage nuts, which are ordered separately
  - Swing-Out Rack Frame assemblies are supplied with mounting supports. Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights.
  - 2. Swing-out mounting supports mount to inside of frame at any vertical location.
  - Mounting supports and swing-out frame can be located deeper into frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame.

#### **BULLETIN: P20**

1

- Swing-Out Rack Frame assemblies are supplied with mounting supports. Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights.
- 2. Swing-out mounting supports mount to inside of frame at any vertical location.
- 3. Mounting supports and swing-out frame can be located deeper into frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame.

#### BULLETIN: P20




Catalog Number	Fits Frame Width	Rack Units
PSF6	600	16
PSF8	800	16

Catalog Number	H mm/in.	W mm/in.	Rack Units	Fits Frame Height	Fits Frame Width
PSF76	538	496	10	700 or taller	600
DAFE	21.18	19.53	40	500	500
PSF77	538 21.18	496 19.53	10	700 or taller	700
PSF78	538 21.18	496 19.53	10	700 or taller	800
PSF146	1215 47.83	496 19.53	25	1400 or taller	600
PSF148	1215 47.83	496 19.53	25	1400 or taller	800
PSF168	1438 63.58	496 19.53	30	1600 or taller	800
PSF186	1615 63.58	496 19.53	34	1800 or taller	600
PSF188	1615 63.58	496 19.53	34	1800 or taller	800
PSF206	1838 72.36	496 19.53	39	2000 or taller	600
PSF207	1838 72.36	496 19.53	39	2000 or taller	700
PSF208	1838 72.36	496 19.53	39	2000 or taller	800
PSF226	2015 79.33	496 19.53	43	2200 tall	600
PSF227	2015 79.33	496 19.53	43	2200 tall	700
PSF228	2015 79.33	496 19.53	43	2200 tall	800

Hoffman

Standard 120° Frame Hinging





#### **170-DEGREE HINGE KIT A-T-O**


Use this kit in conjunction with the Heavy-Duty Swing-Out Frame. It provides increased accessibility to the back of rack equipment.

**BULLETIN: P20** 

Catalog Number PSF170K

Fits Cabine 600, 700 and 800





87415129

Hoffman

# SWING-OUT GUIDES A-T-O

Guides can be mounted to a Heavy-Duty Swing-Out Rack Frame to provide extra support for rack equipment. Plated steel guides are furnished in pairs with mounting hardware included.

## BULLETIN: P20

Catalog Number	Description	
PSFG	Swing-Out Guides	

# STOP ARM KIT A-T-O

Used with Heavy-Duty Swing-Out Rack Frames to lock the frame in the open position. Consists of stop arm and mounting hardware.

# BULLETIN: P20


Catalog Number	Description
PSAK120	120-degree Stop Arm Kit


## FILLER PANEL KIT

Used when mounting Heavy-Duty Swing-Out Rack Frames in 700or 800-mm wide frames. The Filler Panel occupies the extra space between the frame and the swing frame. Includes a handle and all the hardware for mounting to the Swing-Out Rack Frame.

### **BULLETIN: P20**

	Swing		
Catalog Number	Frame Height	Enclosure Width	Mounting
PFPK77LR	700	700	Left or Right
PFPK78C	700	800	Center
PFPK147LR	1400	700	Left or Right
PFPK148C	1400	800	Center
PFPK167LR	1600	700	Left or Right
PFPK168LR	1600	800	Left or Right
PFPK168C	1600	800	Center
PFPK187LR	1800	700	Left or Right
PFPK188LR	1800	800	Left or Right
PFPK188C	1800	800	Center
PFPK208LR	2000	800	Left or Right
PFPK208C	2000	800	Center
PFPK227LR	2200	700	Left or Right
PFPK228LR	2200	800	Left or Right
PFPK228C	2200	800	Center





87794538

87794539

87415128