



Cable Management Spools can be Located Along the Length of the Channel for Proper Cable Routing.

Assembles Quickly: Channels Clip to Equipment Rack.

Pass-Thru Holes Permit Cable Routing from the Front to the Rear of the Rack when Required.

FEATURES

- Rugged construction - Z-Frame withstands abuse.
- Universal hole pattern on rack uprights mates with other rack/channel models.
- Easy-to-use screws with dog-nose tip lead in and #3 Phillips combo head provided.

SPECIFICATIONS

- ◆ Channel Material:
 - "Z" Frame: 14 ga. cold rolled steel.
 - "C" Channel: 16 ga. cold rolled steel.
- ◆ Cover material: 16 ga. cold rolled steel.
- ◆ Finish: Durable black or aluminum color powder coat finish.

APPROVALS/INSTALLATION

- U.S. Patent No. 6,347,714.
- UL Listed File No. E154937.
- Packaged to meet Telcordia GR-63-CORE transportation requirements.

APPLICATIONS

Use in data centers, the equipment room, and telecommunications room to provide racking, cable management, grounding, and power distribution for network hardware.

HUBBELL **NextFrame** Vertical Cable Management

SteadFast™ Gates
ensure proper bend radius.

Cable Management
Organize cable by groups and bundles.

Front covers
conceal cables and easily snap in place.

Optional Hinged Covers
Swings both left and right hand.



"C" Channel Vertical Organizer.

NEXTFRAME® Vertical Cable Channels are the most durable and easy-to-use channels ever developed.

Hubbell's innovative design incorporates many patent-pending, labor-saving features that speed assembly and simplify maintenance. Unparalleled durability ensures long-lasting reliability.

Most important, **NEXTFRAME®** Vertical Cable Channels protect cable by eliminating cold flow and maintaining the proper bend radius of cables entering and exiting the organizer ensuring maximum cable transmission performance.

Vertical Organizers with Hinged Covers



Delivery: 2 Z channels, 38.5"H x 10.5"D, 2 38.5" Covers, 4 Gates, 24 Spools, 4 Hinges, 2 1/2"-13x1" Bolt w/nut and lock washer.

Color	Rack Height	Catalog No. 6"W	Catalog No. 4 1/2"W	Catalog No. 3 1/4"W
Black	7' (2134)	VS76H	VS74H	VS73H

Vertical Organizers



'Z' Channel, 6" with Cover

For 7' or 8' rack. Suitable for approximately 800 4-pair UTP cables when fully utilized.*

Delivery: VS76(A)		Delivery: VS86(A)	
2 Z channels	38.50" x 6" x 10.5"	2 Z channels lower	45.38" x 6" x 10.5"
2 Covers	38.50" x 6"	2 Covers upper	38.50" x 6"
4 Gates		2 Covers lower	45.38" x 6"
2 Bolts, nuts, washers	1/2" - 13 x 1"	2 Covers upper	38.50" x 6"
24 Spools		4 Gates	
		24 Spools	
		2 Bolts, nuts, washers	1/2" - 13 x 1"

Rack Height	Catalog No. Black	Catalog No. Aluminum
7' (2134) or 7.5' (2286)	VS76	VS76A
8' (2438)	VS86	VS86A

'Z' Channel, 6" (for short racks)

Delivery:		
1 Z channel	38.50" x 6" x 10.5	8 Gates
1 Bolts, nut, washer	1/2" - 13 x 1"	

Rack Height	Catalog No. Black	Catalog No. Aluminum
4' (1219) and 5.5' (1676)	VS46	VS46A



'Z' Channel, 4 1/2" wide

Suitable for approximately 540 4-pair UTP cables when fully utilized.*

Delivery:		
2 Z channels	38.50" x 4.5" x 10.5"	16 Gates
2 Bolts, nuts, washers	1/2" - 13 x 1"	

Rack Height	Catalog No. Black
7' (2134)	VS74

'C' Channel, 4 1/2" wide and 3 1/4" wide

Suitable for approximately 300 4-pair UTP cables.

Delivery: VS73(A)		
2 C channels	38.50" x 3.25" x 10.5"***	8 Gates
2 Bolt, nut, washer	1/2" - 13 x 1"	

Rack Height	Catalog No. Black	Catalog No. Aluminum
7' (2134)	VS73	VS73A

* Capacity of front and rear of channel combined.

** When optional rear gates are used.

Gates

Features/Benefits

- Rolled edges ensure proper bend radius and eliminate pinching/chafing of cable.
- Can be located as needed along the channel length for proper cable routing.
- Use extra gates to provide additional cable routing.

Specifications

- ◆ Finish: Durable black or aluminum color powder coat.
- ◆ 14 ga. cold rolled steel.



Order Information

Delivery: 1 kit of 16 gates

Channel Width	6" Width	4½" Width	3¼" Width
Finish	Catalog No.	Catalog No.	Catalog No.
Black	VCG6	VCG4	VCG3
Aluminum	VCG6A	VCG4A	VCG3A

Vertical Cable Management Accessories

Covers

Features/Benefits

- Conceal cable to provide clean appearance.
- Snap in place - no fasteners to wear or break.

Specifications

- ◆ Material: 16 ga. cold rolled steel.
- ◆ Finish: Durable black or aluminum color powder coat finish.

Order Information

Delivery: 1 Cover

	38.5"H	38.5"H	45.38"H	45.38"H
Cover	Black	Aluminum	Black	Aluminum
Width	Catalog No.	Catalog No.	Catalog No.	Catalog No.
6"	VCC6	VCC6A	VCC6L	VCC6AL
4"	VCC4	-	VCC4L	VCC4AL
3"	VCC3	VCC3A	VCC3L	VCC3AL



VCC6

Hinge Kit

Features/Benefits

- Allows cover to be hinged left and right during moves, adds and changes.

Specifications

- ◆ Material: 14 ga. cold rolled steel.

Order Information

Delivery: 2 hinges and fasteners.

Catalog No. **VCKH**

NOTE: Gates not provided, order separately.



Fiber Spools



Features/Benefits

- Used to take up fiber jumper slack in vertical channels.
- 6" wide "Z" frame only.
- Fastens to channel pass-thru holes.

Specifications

- ◆ Material: ABS, Black.

Order Information

Delivery: 5 sets of fiber spools

Catalog No. **VCF610**

Joining Kit



Features/Benefits

- Join top and bottom channel sections when mounting to other than Hubbell racks.
- Join racks side-to-side.

Specifications

- ◆ Finish: durable black powder coat.

Order Information

Delivery: 1 joining plate, 4 #12-24 x 5/8 screws, nuts, washers, 4 1/2"-13 bolts, nuts, washers

Catalog No. **VCJK**

Vertical Rings



MCCVMR2

MCCVMR22

Features/Benefits

- Attaches to front or rear 19" mounting holes on equipment racks.

Specifications

- ◆ Width: 6" (152); depth: 10" (254).
- ◆ Material: 11 ga. cold rolled steel.
- ◆ Finish: Durable, black powder coat.

Order Information

Delivery: 2 vertical rings and 1 mounting kit

Brackets	One side	Both sides
Catalog No.	MCCVMR2	MCCVMR22



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

DS-M12 06/07

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific Hubbell Canada Inc.	852-2836-7131 905-839-1138	Fax: 852-2836-7132 Fax: 905-839-9108	Hubbell Premise Wiring, Latin America Hubbell de Mexico, S.A. de C.V.	305-408-4501 (5255) 9151-9999	Fax: 305-408-8201 Fax: (5255) 9151-9989
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616	Hubbell Premise Wiring, Middle East Hubbell Premise Wiring, Puerto Rico	971-4-393-4192 787-855-1075	Fax: 971-4-393-4194 Fax: 787-855-3265
Hubbell Premise Wiring, China	86-21-6374 2660	Fax: 86-21-6374 2799	Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400	Hubbell Premise Wiring, Venezuela	58-212-5156482	Fax: 58-212-6627258
Hubbell Premise Wiring, India	91-80-4022-4089	Fax: 91-80-4022-4033			
Hubbell Int'l. Inc., Korea Branch	(82 2) 2607 1363	Fax: (82 2) 2603 7386			