









Cast Covers

FEATURES-SPECIFICATIONS



Stamped Material/Finish **Aluminum**

- 316 Stainless steel screws
- Natural finish

Galvanized Steel

- 316 Stainless steel screws
- Natural finish

STAMPED ALUMINUM AND STAMPED STEEL COVERS									
CATALOG NUMBER			DIMENSIONS						
KILLARK ALUMINUM	STAMPED STEEL	HUB SIZE	LENGTH	WIDTH	HEIGHT				
170SA	170	1/2"	3-11/16" (94)	1-3/8" (35)	5/16" (8)				
270SA	270	3/4"	4-1/4" (108)	1-1/2" (32)	5/16" (8)				
370SA	370	1"	5" (127)	1-3/4" (44)	5/16" (8)				
470SA	470	1-1/4"	5-1/2" (140)	2-3/16" (56)	5/16" (8)				
570SA	570	1-1/2"	6" (152)	2-7/16" (62)	5/16" (8)				
670SA	670	2"	7" (178)	3" (76)	5/16" (8)				
870SA	870	2-1/2"	9" (229)	4-1/4" (108)	9/16" (14)				
870SA	870	3"	9" (229)	4-1/4" (108)	9/16" (14)				
970SA	970	3-1/2"	11" (279)	5-1/4" (133)	9/16" (14)				
970SA	970	4"	11" (279)	5-1/4" (133)	9/16" (14)				

Cast Material/Finish

Copper-free Aluminum (less than 4/10 of 1%)

 Electrostatically applied powder coating

Duraloy Class 30 Gray Iron Alloy


- Tri-coat finish of electrozinc, chromate sealant, and electrostatically applied powder coating
- 316 Stainless steel screws

CAST ALUMINUM AND CAST IRON COVERS								
CATALOG NUMBER			DIMENSIONS					
KILLARK ALUMINUM	DURALOY IRON	HUB SIZE	LENGTH	WIDTH	HEIGHT			
170CSA	170C	1/2"	3-11/16" (94)	1-3/8" (35)	3/8" (10)			
270CSA	270C	3/4"	4-1/4" (108)	1-1/2" (32)	3/8" (10)			
370CSA	370C	1"	5" (127)	1-3/4" (44)	3/8" (10)			
470CSA	470C	1-1/4"	5-1/2" (140)	2-3/16" (56)	3/8" (10)			
570CSA	570C	1-1/2"	6" (152)	2-7/16" (62)	3/8" (10)			
670CSA	670C	2"	7" (178)	3" (76)	3/8" (10)			
870CSA	870C	2-1/2"	9" (229)	4-1/4" (108)	3/8" (10)			
870CSA	870C	3"	9" (229)	4-1/4" (108)	3/8" (10)			
970CSA	970C	3-1/2"	11" (279)	5-1/4" (133)	3/8" (10)			
970CSA	970C	4"	11" (279)	5-1/4" (133)	3/8" (10)			

Dimensions

Stamped Covers

LENGTH



Cast Covers





