



Pendant



Ceiling



Wall



Cone Top



25° Stanchion



Straight Stanchion



EZ Adapter*
VMEZA



Tank Adapter
See next page to order

CERTILITE® VM MOUNTING SPLICE BOXES							
CATALOG NUMBER							
HUB SIZE	PENDANT	CEILING 4 HUB	CEILING 5 HUB	WALL	CONE TOP	25 DEGREE STANCHION	90 DEGREE STANCHION
3/4"	VMA2B	VMX2B	VMX6B	VMB2B	VMC2B	—	—
1"	VMA3B	VMX3B	VMX7B	VMB3B	VMC3B	—	—
1-1/4"	—	—	—	—	—	VMD4B	VMS4B
1-1/2"	—	—	—	—	—	VMD5B	VMS5B
M-20	—	VMX8B**	VMX9B	—	—	—	—

*VMEZA is used between a ballast tank and an EZ mount - ordered separately. See catalog grids.

**VMX8B furnished with 3 non-metallic plugs.

VM4L LED OPTICS AND ACCESSORIES		
DESCRIPTION	OPTIC LOGIC	GUARD ^⑤
Flat Lens (glass spin top) "C" tank only	VZRGF12 (GF)	VZRF12GRD
Flat Lens (polycarbonate spin top) "C" tank only	VZRPF12 (PF)	VZRF12GRD
Globe (glass)	VMG25 (GL)	VMAG25S
Reflector (all glass) Type I	VMR251 (R1)	VMAG25S
Reflector (all glass) Type III	VMR253 (R3)	VMAG25S
Reflector (all glass) Type V	VMR255 (R5)	VMAG25S
Enclosed Reflector	VMER40 (ER)	VMERG
Enclosed Reflector with Polycarbonate Lens*	VMEP40 (EP) ^④	—
Reflector (Polycarbonate spin top) 12" Type V*	VZRP175B (P5)	VMRWGS
Reflector (glass spin top) 12" Type V	VZRG4050 (S5)	VMRWGS
Reflector (glass spin top) 12" Type II	VZRG4020 (S2)	VMRWGS
Globe (Silicone coated)	VMG25F (FG)	VMAG25S
Globe Teflon [®] coated ^①	VMG25T (TG)	VMAG25S
Reflector Teflon [®] coated (all glass) Type I	VMR251T (T1)	VMAG25S
Reflector Teflon [®] coated (all glass) Type III	VMR253T (T3)	VMAG25S
Reflector Teflon [®] coated (all glass) Type V	VMR255T (T5)	VMAG25S
Reflector Teflon [®] coated (spin top) 12" Type V	VZRG4050T (TV)	VMRWGS
Reflector Teflon [®] coated (spin top) 12" Type II	VZRG4020T (T2)	VMRWGS

*Non-glass over Food/Grain Class II Div 1 Group G Certified; VMEP40, VZRP175B, and VZRPF12

^① Teflon is a registered trademark of DuPont, Inc.

VM4L LED REFLECTORS AND ACCESSORIES	
DOME REFLECTOR (Polyester reinforced fiberglass)	VMPD40
ANGLE REFLECTOR (Polyester reinforced fiberglass)	VMPA40
DEEP DOME REFLECTOR (White Painted Aluminum)	HRD400
DEEP DOME REFLECTOR (Anodized Aluminum)	HRD400ALZ
120VAC Photocell with FS Style Cover ^②	VMFSPC1
208-277VAC Photocell with FS Style Cover ^②	VMFSPC2
Bottom Closure for VMAG25S ^⑤	VMAGBC
4-sided EXIT Accessory (use without guard) ^③	VEXA400

^② Order single-gang FS box separately. For photocell factory installed in tank, see logic.

^③ For use with Generator or UPS powered fixtures

^④ For wall applications mount must be spaced out for bottom hub

^⑤ Guards are 316 Stainless. Bottom closure for VMAG25S pt. no. VMAGBC



VMG25



VMR255
VMR253
VMR251



VMAG25S



VMAGBC



VMER40



VMERG



VMEP40



VZRG4050
VZRG4020



VMRWGS



VZRPF/VZRGF



VMPD40

Standard Dome, Fiberglass
White Reflector, Dia: 16"



VMPA40

30° Angle, Fiberglass
White Reflector, Dia:16"



HRD400

Deep Aluminum, White
Reflector, Dia: 21"



HRD400ALZ

Deep Aluminum, Anodized
Reflector, Dia: 21"



VMFSPC



VEXA400
Fixture not included