



netSELECT® Patch Panels are excellent for designing rack systems for telephone, data and AV systems. Consolidation Blocks are ideal for small user count configurations that mount in or on the wall.

- Meets ANSI/TIA - Category 6 and Category 5e standards
- cULus Listed

**Universal Consolidation Blocks and Patch Panels**

| Description  | Catalog Number                   |
|--|----------------------------------|
| Category 5e 12-Port Universal Consolidation Block, 89D Bracket Mount   | <b>NS5E12U</b>                   |
| Category 6 12-Port Universal Consolidation Block, 89D Bracket Mount  | <b>NS612U</b>                    |
| Category 5e Universal Patch Panel<br>24-port, 1.75 inch H, 1 Rack Unit<br>48-port, 3.50 inch H, 2 Rack Units | <b>NS5E24U</b><br><b>NS5E48U</b> |
| Category 6 Universal Patch Panel<br>24-port, 1.75 inch H, 1 Rack Unit<br>48-port, 3.50 inch H, 2 Rack Units  | <b>NS624U</b><br><b>NS648U</b>   |



**NS5E12U**



**NS612U**



**NS5E24U**



**NS5E48U**



**NS624U**



**NS648U**

netSELECT® Patch Cords allow for quick change of voice/data lines with insertion of modular plugs.

- Meets and exceeds ANSI/TIA - Category 6 and Category 5e standards
- UL and cUL Listed

**Universal Patch Cords, Category 6 and Category 5e**

| Description        | Color  | 1-Foot          | 3-Foot          | 5-Foot          | 7-Foot          | 10-Foot         | 15-Foot         | 20-Foot         | 25-Foot         |
|--------------------|--------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| Cat. 5e Patch Cord | Blue   | <b>HC5EB01</b>  | <b>HC5EB03</b>  | <b>HC5EB05</b>  | <b>HC5EB07</b>  | <b>HC5EB10</b>  | <b>HC5EB15</b>  | <b>HC5EB20</b>  | <b>HC5EB25</b>  |
|                    | Gray   | <b>HC5EGY01</b> | <b>HC5EGY03</b> | <b>HC5EGY05</b> | <b>HC5EGY07</b> | <b>HC5EGY10</b> | <b>HC5EGY15</b> | <b>HC5EGY20</b> | <b>HC5EGY25</b> |
|                    | Yellow | <b>HC5EY01</b>  | <b>HC5EY03</b>  | <b>HC5EY05</b>  | <b>HC5EY07</b>  | <b>HC5EY10</b>  | <b>HC5EY15</b>  | <b>HC5EY20</b>  | <b>HC5EY25</b>  |
|                    | Red    | <b>HC5ER01</b>  | <b>HC5ER03</b>  | <b>HC5ER05</b>  | <b>HC5ER07</b>  | <b>HC5ER10</b>  | <b>HC5ER15</b>  | <b>HC5ER20</b>  | <b>HC5ER25</b>  |
| Cat. 6 Patch Cord  | Blue   | <b>HC6B01</b>   | <b>HC6B03</b>   | <b>HC6B05</b>   | <b>HC6B07</b>   | <b>HC6B10</b>   | <b>HC6B15</b>   | <b>HC6B20</b>   | <b>HC6B25</b>   |
|                    | Gray   | <b>HC6GY01</b>  | <b>HC6GY03</b>  | <b>HC6GY05</b>  | <b>HC6GY07</b>  | <b>HC6GY10</b>  | <b>HC6GY15</b>  | <b>HC6GY20</b>  | <b>HC6GY25</b>  |
|                    | Yellow | <b>HC6Y01</b>   | <b>HC6Y03</b>   | <b>HC6Y05</b>   | <b>HC6Y07</b>   | <b>HC6Y10</b>   | <b>HC6Y15</b>   | <b>HC6Y20</b>   | <b>HC6Y25</b>   |
|                    | Red    | <b>HC6R01</b>   | <b>HC6R03</b>   | <b>HC6R05</b>   | <b>HC6R07</b>   | <b>HC6R10</b>   | <b>HC6R15</b>   | <b>HC6R20</b>   | <b>HC6R25</b>   |