



HUBBELL
Advantage

- Third Party Verified Category 6 Component Exceeds TIA Limits
- Plug Optimized for High Density Switch Port Count
- Supports 10/100/1000BASE-T
- PoE+ Ready



Specifications



- Cable construction:
 - Conductor: 24AWG UTP
 - Jacket: flame-retardant PVC – CM rated

Standards/Listings/Verifications

- TIA-568-C.2 Category 5e and 6 components
- UL Listed 1863

NEXTSPEED® Category 6 Patch Cords

Length	Catalog No.	Length	Catalog No.
3'	HC6xx03	15'	HC6xx15
5'	HC6xx05	20'	HC6xx20
7'	HC6xx07	25'	HC6xx25
10'	HC6xx10		

xx = Color: **B** (Blue), **BK** (Black), **GN** (Green), **GY** (Gray), **OR** (Orange), **P** (Purple), **R** (Red), **W** (White) and **Y** (Yellow). See color chart on page V30.
Made-to-order lengths are available from 30ft to 100ft in 5ft increments.



HC6B03

SPEEDGAIN® Category 5e Patch Cords

Length	Catalog No.	Length	Catalog No.
1'	HC5Exx01	10'	HC5Exx10
3'	HC5Exx03	15'	HC5Exx15
5'	HC5Exx05	20'	HC5Exx20
7'	HC5Exx07		

xx = Color: **B** (Blue), **BK** (Black), **GN** (Green), **GY** (Gray), **OR** (Orange), **P** (Purple), **R** (Red), **W** (White) and **Y** (Yellow). See color chart on page V30.
Made-to-order lengths are available from 25ft to 100ft in 5ft increments.



HC5ER03

SPEEDGAIN® Shielded Category 5e Patch Cords

Length	Catalog No.	Length	Catalog No.
3'	PS5E03xx	15'	PS5E15xx
5'	PS5E05xx	20'	PS5E20xx
7'	PS5E07xx	25'	PS5E25xx
10'	PS5E10xx		

xx = Color: **B** (Blue) and **GY** (Gray). See color chart on page V30.



PS5E10GY