






Wallplates and Face Plates

Nylon and Metal Wallplates

	Description	Color	Toggle Switch Plates		Duplex Receptacle Plates		GFCI, Surge & Style Line® Receptacle Plates	
			1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang
 NP1AL	Standard, Smooth High-Impact Nylon.	Almond	NP1AL	NP2AL	NP8AL	NP82AL	NP26AL	NP262AL
		Ivory	NP1I	NP2I	NP8I	NP82I	NP26I	NP262I
		White	NP1W	NP2W	NP8W	NP82W	NP26W	NP262W
		Brown	NP1	NP2	NP8	NP82	NP26	NP262
		Gray	NP1GY	NP2GY	NP8GY	NP82GY	NP26GY	NP262GY
		Office White	NP1OW	NP2OW	NP8OW	NP82OW	NP26OW	NP262OW
		Black	NP1BK	NP2BK	NP8BK	NP82BK	NP26BK	NP262BK
		Red	NP1R	NP2R	NP8R	NP82R	NP26R	NP262R
		Orange	—	—	NP8OR	NP82OR	—	—
		 NP8AL	Plated Steel.	Chrome	SCH1	SCH2	SCH8	SCH82
Brass	SBP1			SBP2	SBP8	SBP82	SBP26	SBP262
 NP26AL	Stainless Steel.	Smooth	SS1	SS2	SS8	SS82	SS26	SS262
		Beveled	97071	—	97101	—	—	—
	Brass.	Smooth	SB1	SB2	SB8	SB82	SB26	SB262
		Smooth	SA1	SA2	SA8	SA82	—	—
	Anodized Aluminum.	Smooth	SA1	SA2	SA8	SA82	—	—

Duplex and Style Line® Plates











IFP18AL














IFP126AL

Description	Color	Catalog Numbers
Duplex Plate with label fields. (Accepts Duplex Frames)	Almond	IFP18AL
	Gray	IFP18GY
	Office White	IFP18OW
Style Line® Plate with label fields. (Accepts Style Line Frames)	Almond	IFP126AL
	Gray	IFP126GY
	Office White	IFP126OW

IFP Face Plates

Color	1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 6-Port	9-Port	12-Port
								
Almond	IFP11AL	IFP12AL	IFP13AL	IFP14AL	IFP16AL	IFP26AL	IFP29AL	IFP212AL
Gray	IFP11GY	IFP12GY	IFP13GY	IFP14GY	IFP16GY	IFP26GY	IFP29GY	IFP212GY
Office White	IFP11OW	IFP12OW	IFP13OW	IFP14OW	IFP16OW	IFP26OW	IFP29OW	IFP212OW
Black	IFP11BK	IFP12BK	IFP13BK	IFP14BK	IFP16BK	IFP26BK	IFP29BK	IFP212BK
Electric Ivory	IFP11EI	IFP12EI	IFP13EI	IFP14EI	IFP16EI	IFP26EI	IFP29EI	IFP212EI
White	IFP11W	IFP12W	IFP13W	IFP14W	IFP16W	IFP26W	IFP29W	IFP212W

SSF Stainless Steel Plates

1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 4-Port	6-Port	9-Port	12-Port
								
SSF11	SSF12	SSF13	SSF14	SSF16	SSF204	SSF206	SSF209	SSF212
With Label Fields						Keystone Opening Hole size for mounting all Hubbell Jacks B  A: .580" (14.73) B: .760" (19.30)		
1-Port	2-Port	3-Port	4-Port	6-Port				
SSFL11	SSFL12	SSFL13	SSFL14	SSFL16				

Note: All SSF plates will accept Audio/Video keystone connectors and Xcelerator™ jacks.

