

FXS SERIES • CONTROLS
FACTORY SEALED TUMBLER SWITCHES AND
GROUND FAULT INTERRUPTER



Tumbler Switches

Ground Fault Interrupter



For GFI Protection with receptacle, See page PR26
Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
NEMA 3, 7(C,D) 9(E,F,G)

FEATURES-SPECIFICATIONS

Applications

FXS Tumbler Switches are suitable for applications where making, breaking or changing connections in an electrical circuit is required and where conditions of load do not exceed the switch ratings.

Listed - File E53360 and/or Ffile E10501

Certified - File LR11714
 See files for details or call Killark.

Applications

FXS Ground Fault Interrupters are designed to interrupt a circuit when a ground fault is detected on equipment which may be handled by personnel in hazardous locations.

Features

- Test and Reset push buttons are provided on cover assembly. Unit should be tested monthly
- Includes new GFI to meet latest UL943 GFCI standards revisions
- Exterior gasket provides NEMA 3 weatherproof protection
- Ground boss for grounding in the splice box
- Color coded wiring
- Captive cover bolts are made from stainless steel

Electrical Rating

GFI units are rated at 20A, 120 VAC, 60HZ. Class A.
 4-6 milliamp trip setting
 Trip Time-UL Curve

Listed - File E80595

Certified - File LR61895
 See files for details or call Killark.

FXS TUMBLER SWITCHES					
CATALOG NUMBER			HUB SIZE	SWITCH STYLE	SWITCH RATING 120/277 VAC, 1Ø
COMPLETE UNIT					
COVER WITH SWITCH	(BOX, COVER AND SWITCH)				
	DEAD-END	FEED-THRU			
FXS-1C	FXS-11C	FXS-41C	1/2"	1-POLE	20 A [Ⓢ]
	FXS-21C	FXS-51C	3/4"		
FXS-2C	FXS-12C	FXS-42C	1/2"	2-POLE	20 A [Ⓢ]
	FXS-22C	FXS-52C	3/4"		
FXS-8C	FXS-18C	FXS-48C	1/2"	3-POLE	Ⓢ
	FXS-28C	FXS-58C	3/4"		
FXS-3C	FXS-13C	FXS-43C	1/2"	3-WAY/ SPDT (No off)	20 A [Ⓢ]
	FXS-23C	FXS-53C	3/4"		
FXS-5C	FXS-15C	FXS-45C	1/2"	SPDT (Center off)	20 A [Ⓢ]
	FXS-25C	FXS-55C	3/4"		
FXS-6C	FXS-16C	FXS-46C	1/2"	DPDT (No off)	20 A [Ⓢ]
	FXS-26C	FXS-56C	3/4"		
FXS-1D	FXS-11D	FXS-41D	1/2"	1-POLE	30 A [Ⓢ]
	FXS-21D	FXS-51D	3/4"		
FXS-2D	FXS-12D	FXS-42D	1/2"	2-POLE	30 A [Ⓢ]
	FXS-22D	FXS-52D	3/4"		
FXS-4C	—	—	—	4-WAY	20 A [Ⓢ]

[Ⓢ]Rated 15 amperes, 240/480 VAC., 3Ø; 3HP-240 VAC., 5 HP-480 VAC.

[Ⓢ]Horsepower rated 1 HP at 120 VAC, 2 HP at 240 VAC.

FXS GROUND FAULT INTERRUPTER†				
CATALOG NUMBER			HUB SIZE	
COMPLETE UNIT	COVER ASSEMBLY	BACK BOX*	DEAD END	
FXS-GFI-1020	FXS-GFI03	FXB-1		
FXS-GFI-2020	FXS-GFI03	FXB-2	3/4"	
FXS-GFI-3020	FXS-GFI03	FXB-3	1"	
FXS-GFI-1120	FXS-GFI03	FXB-4	FEED THRU	1/2"
FXS-GFI-2120	FXS-GFI03	FXB-5		3/4"
FXS-GFI-3120	FXS-GFI03	FXB-6		1"

For control stations with 1" conduit opening or for double gang assemblies, order cover with device and box as separate components.

*Boxes and covers shipped separately.

†See page DE25 for additional ground fault control stations.

FXS GROUND FAULT INTERRUPTER WITH LED LAMP	
CATALOG NUMBER FOR COVER ASSEMBLY	FXS-GFI03PL

* Order FXB back box as separate item.



KILLARK®