



Precision Cleaver  
OFCLV5



Buffer Strip Tool  
OFSTRIP



Fiber Test Set  
OFPM813, OFLS813



Fiber Microscope  
OFSCOPE1



Epoxy Termination Kit  
OFTK03C

## Fiber Cleavers

Description	Catalog No.
Multimode fiber only	<b>OFCLV3</b>
SM or MM fiber, CT-30 style, with case	<b>OFCLV4</b>
SM or MM fiber, precision, with case	<b>OFCLV5</b>

## Visual Fault Locators (ST, SC, LC)

Includes: batteries, LC adapter, holster, wrist strap and end protectors

Description	Catalog No.
Visual fault locator	<b>OFVFLKT1</b>
LC adapter, separate	<b>OFVLCADP</b>

*TIP: Use a VFL during termination for optimum test results.*

## Microscope, 400X

Includes: built-in illuminator, batteries, SC/ST-style adapter, and soft pouch

Description	Catalog No.
SC/ST-style microscope	<b>OFSCOPE1</b>
LC adapter (400X microscope only)	<b>FOADPTLC</b>

## Fiber Strip Tools

Description	Catalog No.
900 micron buffered fiber	<b>OFSTRIP</b>
Universal 250/900μ, 2.0, 2.5, 3.0mm cable	<b>OFSTRIP2</b>

## Multimode Test Set

Includes: (1) power meter, (1) dual wavelength LED source, (1) soft pouch, batteries

Description	Catalog No.
Complete tester kit	<b>OFPLK813A</b>
Power meter dual wavelength	<b>OFPM813</b>
LED light source dual wavelength, multimode	<b>OFLS813</b>

## Microscope, 200X (ST, SC, LC)

Includes: batteries, LC adapter, and soft pouch

Description	Catalog No.
ST, SC, LC microscope	<b>OFSCOPE2</b>

## Field Installation Tool Kit, Epoxy and Crimp Style

Includes:

- OFSTRIP2 fiber strip tool
- OFCMT04 crimp tool
- Universal 2.5mm and 1.25mm polishing pucks
- Polishing plate
- 70 durometer polishing pad
- Polishing paper
- 200X microscope with 2.5mm and 1.25mm universal adapters
- Carbon fiber scissors
- Reversible blade carbide scribe
- Permanent marker
- Protective glasses
- Debris bottle for fiber safety
- Alcohol wipes
- Lint free cleaning wipes
- Water bottle
- Alcohol bottle
- 6" ruler
- 10" long x 7" wide x 6.25" high carrying case with the lid functioning as a portable work surface

Description	Catalog No.
Field installation tool kit for SC/ST and LC connectors	<b>OFTK05</b>

## Kevlar® Cable Scissors

Description	Catalog No.
For cutting Kevlar reinforced cables up to 24-strand, non-armored	<b>OFSCSRS</b>

## Connector Installation Tool Pouch

Includes: sapphire scribe, scribe guide, black permanent marker, carbon fiber scissors, strip template and polishing fixture, ruler, buffer/cable jacket stripper, 200X microscope assembly, crimp tool and die

Description	Catalog No.
For SC/ST-style connectors crimp or adhesive termination	<b>OFTP02C</b>

## Termination Kits, Epoxy

Includes: canned air, 10oz, tool pouch (OFTP02C) with fiber and cable preparation tools, wipes, heat cure epoxy, anaerobic adhesive and primer, polishing paper, polishing pad, heat-cure epoxy oven, safety glasses, syringes, needles, cure adapters and clips

For SC/ST-style connectors	Catalog No.
16-Port (110V AC)	<b>OFTK03C</b>
8-Port (220V AC)	<b>OFTK04C*</b>

\*Does not contain canned air.



Epoxy/Crimp Termination Kit  
OFTK05

Note: See PROclick® connectors on page G3 for termination tool applications. Kevlar is a registered trademark of E. I. du Pont de Nemours and Company.