



Equipment Shelves for Server Cabinets

Telescopic Shelf Provides a Slide-Out Surface Featuring Rear Access.

Stationary Shelf Perforated for Ventilation.

Ideal for Monitors, Modems, External Drives and Manuals.



Equipment Shelf, Stationary

SPECIFICATIONS

- ◆ Material: 16 ga. steel.
- ◆ Finish: Durable black, powder coat.
- ◆ Load capacity: 200 lbs.
- ◆ Screw style: #12-24.
- ◆ Dimensions: 16.9"W x 28.2"D.

ORDER INFORMATION

Delivery: 1 shelf, 2 mounting brackets and 3 mounting screws.

Color	Catalog. No.
Black	CKSSD



Equipment Shelf, Telescopic

SPECIFICATIONS

- ◆ Material: 16 ga. steel.
- ◆ Finish: Durable, black powder coat.
- ◆ Load capacity: 200 lbs.
- ◆ Screw style: #12-24.
- ◆ Dimensions: 16.5"W x 29.2"D.

ORDER INFORMATION


Delivery: 1 shelf pre-assembled with telescopic slides and 2 kits mounting hardware.

Color	Catalog. No.
Black	CKTSD



DIMENSIONS

CKSSD



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005

Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
 Hubbell Canada Inc.
 Hubbell Premise Wiring, Central America
 Hubbell Premise Wiring, China
 Hubbell Premise Wiring, Colombia
 Hubbell Premise Wiring, Europe
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131 Fax: 852-2836-7132
 905-839-1138 Fax: 905-839-9108
 506-309-4158 Fax: 506-260-1616
 8621-6309-0119 Fax: 8621-6309-0122
 571-245-8940 Fax: 571-340-0925
 44-01283 500500 Fax: 44-01283 500400
 82-2-(0)2607-1363 Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America
 Hubbell de Mexico, S.A. de C.V.
 Hubbell Premise Wiring, Middle East
 Hubbell-Taian Co., Ltd., Taiwan
 Hubbell Premise Wiring, Turkey
 Hubbell Premise Wiring, Venezuela

305-408-4501 Fax: 305-408-8201
 (5255) 9151-9999 Fax: (5255) 9151-9989
 971-4-393-4192 Fax: 971-4-393-4194
 886-2-2522-1862 Fax: 886-2-2522-1872
 90-216-313-5016 Fax: 90-216-414-8148
 58-416-680-7453 Fax: 58-281-274-7900