



Designed to Accept Industry's Most Extensive Line of Audio/Video Connectors, UTP, Coax, and Fiber Keystone Connectors.

Rear, Flush Mounting Improves Tamper-Resistance.

## Face Plates, Stainless Steel



### FEATURES

- Flush Keystone mounting.
- Single or Double-gang versions available.
- Field configurable.

### SPECIFICATIONS

- ◆ Type 430 stainless steel.
- ◆ Brushed stainless steel finish.
- ◆ Rear housing of Noryl®.
- ◆ 3/4" stainless steel mounting screws supplied.
- ◆ Dimensions:
  - SSF1: 2.75"W x 4.5"H.
  - SSF2: 4.5"W x 4.5"H.

Stainless Steel Faceplates - SSF, are designed for flush mount applications, accepting Hubbell's extensive line of **XCELERATOR™** jacks and Audio/Video connectors that snap mount flush into the keystone opening, creating an elegant streamline look.

This attractive plate can be configured for a multitude of environments such as medical facilities, manufacturing plants, and school systems where reliability, durability, and tamper-resistance are critical elements in choosing the appropriate plate.

### STANDARDS/LISTINGS/VERIFICATIONS

### APPLICATIONS

- ▲ Medical Facilities.
- ▲ Laboratories.
- ▲ Manufacturing Plants.
- ▲ Education Facilities.

**ORDERING INFORMATION**

**SSF Stainless Steel Plates**



	Single-gang					Double-gang			
	1-port	2-port	3-port	4-port	6-port	4-port	6-port	9-port	12-port
Unit Package	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag
Order Qty.	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 10	Carton of 10	Carton of 10	Carton of 10
Catalog No.	<b>SSF11</b>	<b>SSF12</b>	<b>SSF13</b>	<b>SSF14</b>	<b>SSF16</b>	<b>SSF204</b>	<b>SSF206</b>	<b>SSF209</b>	<b>SSF212</b>

NOTE: All SSF plates will accept Audio/Video keystone connectors and XCELERATOR™ jacks.

**SSF Stainless Steel Plate with Label Fields**

**Order Information**

	1-port	2-port	3-port	4-port	6-port
Unit Package	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag
Order Qty.	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 25
Catalog No.	<b>SSFL11</b>	<b>SSFL12</b>	<b>SSFL13</b>	<b>SSFL14</b>	<b>SSFL16</b>



SSFL13

NOTE: All SSF plates will accept Audio/Video keystone connectors and XCELERATOR™ jacks.

**ACCESSORIES**

**XCELERATOR™ Jacks, Category 6 and 5e**

	Catalog No.
Category 5e	<b>HXJ5EXX</b>
Category 6	<b>HXJ6XX</b>

XX = Color:  
 'AL' = Almond      'OW' = Office White  
 'B' = Blue          'OR' = Orange  
 'BK' = Black        'P25' = Purple\*  
 'EI' = Electric Ivory 'R' = Red  
 'GL25' = Gold\*      'TI' = Telco Ivory  
 'GY' = Gray        'W' = White  
 'GN' = Green        'Y' = Yellow  
 \* 25-packs only.



**Patch Cords, Category 6 and 5e**

	Catalog No.
Category 5e	<b>PCX5EXX*</b>
Category 6	<b>PCX6XX**</b>

XX = Standard Color:  
 "B" = Blue; "BK" = Black;  
 "GY" = Gray; "Y" = Yellow  
 For other colors replace color designation with one of the following:  
 OR = Orange, R = Red, GN = Green, P = Purple, W = White

\* = Standard Length: '01'=1'; '03'=3'; '05'=5'; '07'=7'; '10'=10'; '15'=15'; '20'=20'; '25'=25'; '30'=30'; '35'=35'; '40'=40'; '45'=45'; '50'=50'; '55'=55'; '60'=60'; '75'=75'; '100'=100'  
 \*\* = Standard Length: '03' = 3'; '06' = 6'; '08' = 8'; '10' = 10'; '12' = 12'; '16' = 16'; '20' = 20'



**UTP Cable, SPEEDGAIN® Category 5E, 4-Pair**



Color	Catalog No. Riser		Catalog No. Plenum	
	Spool	REELEX*	Spool	REELEX*
Blue	<b>C5EPSRB</b>	<b>C5EPRRB</b>	<b>C5EPSPB</b>	<b>C5EPRPB</b>
Gray	<b>C5EPSRGY</b>	<b>C5EPRRGY</b>	<b>C5EPSPGY</b>	<b>C5EPRPGY</b>
White	<b>C5EPSRW</b>	<b>C5EPRRW</b>	<b>C5EPSPW</b>	<b>C5EPRPW</b>
Yellow	<b>C5EPSRY</b>	<b>C5EPRRY</b>	<b>C5EPSPY</b>	<b>C5EPRPY</b>

\* REELEX is licensed and patented by Windings Inc.

**UTP Cable, NEXTSPEED® Category 6, 4-Pair**



Color	Catalog No. Riser		Catalog No. Plenum	
	Spool	REELEX*	Spool	REELEX*
Blue	<b>C6SRB</b>	<b>C6RRB</b>	<b>C6SPB</b>	<b>C6RPB</b>
Gray	<b>C6SRGY</b>	<b>C6RRGY</b>	<b>C6SPGY</b>	<b>C6RPGY</b>
White	<b>C6SRW</b>	<b>C6RRW</b>	<b>C6SPW</b>	<b>C6RPW</b>
Yellow	<b>C6SRY</b>	<b>C6RRY</b>	<b>C6SPY</b>	<b>C6RPY</b>

\* REELEX is licensed and patented by Windings Inc.



**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific	852-2836-7131	Fax: 852-2836-7132
Hubbell Canada Inc.	905-839-1138	Fax: 905-839-9108
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616
Hubbell Premise Wiring, China	8621-6309-0119	Fax: 8621-6309-0122
Hubbell Premise Wiring, Colombia	571-245-8940	Fax: 571-340-0925
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400
Hubbell Int'l. Inc., Korea Branch	82-2-(0)2607-1363	Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America	305-408-4501	Fax: 305-408-8201
Hubbell de Mexico, S.A. de C.V.	(5255) 9151-9999	Fax: (5255) 9151-9989
Hubbell Premise Wiring, Middle East	971-4-393-4192	Fax: 971-4-393-4194
Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Turkey	90-216-313-5016	Fax: 90-216-414-8148
Hubbell Premise Wiring, Venezuela	58-416-680-7453	Fax: 58-281-274-7900