



netSELECT™

**Communication Products for
Residential Applications
Ordering Guide**



Hubbell Premise Wiring

Network Enclosures



netSELECT™ is an innovative network solution that's perfect for any home or small office. Specifically positioned as the voice/data segment for the homeSELECT™ brand, the netSELECT™ System satisfies the need for a dependable, flexible system that can accommodate all of today's fast-changing voice, data and video requirements. This cost-effective solution incorporates all the quality you'd expect from Hubbell. Built-in flexibility makes it easy to upgrade and keep pace with evolving technologies.



Pre-Configured Network Enclosure 14"H with Hinged Cover

Basic home network kit includes:
 1 box with hinged cover (NSOBOX14)
 1 primary 8-port telephone module (NSOPTM8)
 1 four-way coax splitter module (NSOVDM4)

Catalog No.
NSOBNK14



14" Network Enclosure

Dimensions: 14.38"W x 14"H x 3.96"D.

Knock-outs: Top: two 1½" and three 1½" or 2" combo; Bottom: one 1½" and one 1½" or 2" combo; Back: two 1¼".

Enclosure Description

14" Network Enclosure with hinged cover
 14" Network Enclosure with panel cover

Catalog No.
NSOBOX14
NSOBOX14BC

Components

14"H Box only
 Hinged Door
 Panel cover

Catalog No.
NSOBOX14B
NSOBOX14D
NSOBOX14C



28" Network Enclosure

Dimensions: 14.38"W x 28"H x 3.96"D.

Knock-outs: Top: five 2"; Bottom: 2 power kit knock-outs; Back: eight 1¼".

Enclosure Description

28" Network Enclosure with hinged cover
 28" Network Enclosure with panel cover

Catalog No.
NSOBOX28
NSOBOX28BC

Components

28"H Box only
 Hinged Door
 Panel cover

Catalog No.
NSOBOX28B
NSOBOX28D
NSOBOX28C

48" Network Enclosure

Dimensions: 14.38"W x 48"H x 3.96"D.

Knock-outs: Top: five 2"; Bottom: 2 power kit knock-outs; Back: none.

Enclosure Description

48" Network Enclosure with hinged cover

Catalog No.
NSOBOX48

Network Modules and Accessories

Network Modules

Primary Telephone Module, 8-Port

Supports 8 phone outlets with up to 4 incoming lines for voice, fax or modem applications in a protected PCB module. Pre-mounted push pins snap the module quickly into place. RJ31X interface jack included for security system connection. RJ45 jack interfaces with optional NSOETM8 telephone Expansion module for additional extensions.

Catalog No.
NSOPTM8

Expansion Telephone Module, 8-Port

Adds an additional 8 phone outlets with up to 4 incoming lines when used with the primary telephone module. Pre-mounted push pins snap the module quickly into place. Includes RJ45 jumper cord to connect with NSOPTM8 Primary Telephone module.

NSOETM8

Telephone Module, Multiport Patchable

Terminates lines via modular plug to accommodate flexibility, by changing plug locations. Allows data lines to be converted to voice, with the move of a patch cord. Includes nine RJ45 jumper cords.

NSOMTM24

Data Module, 8-port

Supports Gigabit Ethernet for up to 8 data lines with front 110 punch down terminations in a protected PCB module. Pre-mounted push pins snap the module quickly into place.

Cat 5e: **NSODM8**

Cat 6: **NSODM8C6**

Combination Module, 6-port Telephone, 1-port Data

Provides basic telephone and data delivery in a small package. Allows data lines to be converted to voice, with the move of a patch cord.

NSO6P1DM

Blank Module Plate

Module allows mounting of active components (i.e. switches, routers) or other devices (66 blocks, audio components) onto a modular platform. Can be custom drilled or used with two self-adhesive cable strips included to mount components onto module. Pre-mounted push pins snap the module quickly into place.

NSOBM



Network Accessories

Standard Power Kit

Includes duplex receptacle 15A/125V NEMA 5-15R, electrical steel box and wall plate.

Catalog No.
NSOKP

Surge Suppression Power Kit

Includes surge receptacle 15A/125V NEMA 5-15R, 240 Joules/15,000A protection per mode, electrical steel box and wall plate.

NSOKPS

Lock Kit

Chromed steel, includes 2 keys. Eliminates unwanted tampering.

FLOCK1

Panel Bracket Adapter

For use with Adapter Brackets shown below. Snap mounts into Network Enclosures.

NSOF5B

F-Connector Adapter Panel

Includes six populated coax connectors.

FSPFP6X

Keystone Adapter Panel

Includes six blank openings.

FSPHD6X



Modular Keystone Jacks and AV Connectors

XCELERATOR™ Jacks, Category 6

Supports 10GbE applications to 55 meters, Gigabit Ethernet in the backbone, and network convergence out to the work area with usable bandwidth of 500 MHz in the channel.



Color	Catalog No.	Bag of 25 Catalog No.
See chart below	HXJ6XX	HXJ6XX25
Replace XX with color code: Almond = "AL"; Black = "BK"; Blue = "B"; Gray = "GY"; Green = "GN"; Ivory = "I"; Light Almond = "LA"; Office White = "OW"; Orange = "OR"; Red = "R"; White = "W"; Yellow = "Y".		

XCELERATOR™ Jacks, Category 5e

Supports 10/100/1000BASE-T applications with usable bandwidth of 190 MHz in the channel.



Color	Catalog No.	Bag of 25 Catalog No.
See chart below	HXJ5EXX	HXJ5EALXX
Replace XX with color code: Almond = "AL"; Black = "BK"; Blue = "B"; Gray = "GY"; Green = "GN"; Ivory = "I"; Light Almond = "LA"; Office White = "OW"; Orange = "OR"; Red = "R"; White = "W"; Yellow = "Y".		

XCELERATOR™ Jacks, USOC

Supports voice applications.



Color	Catalog No.	Bag of 25 Catalog No. (Office White only)
See chart below	HXJUXX	HXJUOW25
Replace XX with color code: Almond = "AL"; Black = "BK"; Blue = "B"; Gray = "GY"; Green = "GN"; Ivory = "I"; Light Almond = "LA"; Office White = "OW"; Orange = "OR"; Red = "R"; White = "W"; Yellow = "Y".		

Jack Icons



Color	Blank	Computer	Telephone
See chart below	IXX100	IXX100C	IXX100T
Replace XX with color code: Black = "BK"; Blue = "B"; Brown = "BN"; Gray = "GY"; Green = "GN"; Ivory = "I"; Orange = "OR"; Purple = "P"; Red = "R"; White = "W"; Yellow = "Y".			

F-Type Connectors

Distributes high quality video signal to the workstation. Requiring no soldering, these connectors install with a snap and provide quick, easy "screw-on" termination. Compatible with TV, CATV and CCTV, home theater and entertainment systems, satellite, security and surveillance systems, VCR/DVD applications.



	F-Type Coupler Bulkhead F/F Catalog No.	F-Type Coupler Bulkhead F/F Gold Catalog No.	F-Type to RCA Bulkhead F/F Gold Catalog No.	F-Type Recessed Catalog No.
Almond	SFFALX	SFFGAL	-	SFGRFAL
Almond, Light	SFFLAX	SFFGLA	SFRFGLA	-
Black	SFFBX	SFFGBK	SFRGBK	SFGRFBK
Ivory	SFFEX	SFFGEI	SFRFGEI	SFGRFEI
Gray	SFFGX	SFFGGY	SFRFGGY	SFGRFGY
Office White	SFFX	SFFGOW	SFRFGOW	SFGRFOW
White	SFFWX	SFFGW	SFRFGW	SFGRFW

S-Video Connectors, BNC Connectors

Transmits video information over a cable by dividing the signal into two separate signals (chrominance) for color and (luminance) for brightness. Applications include cable, satellite, DVD, camera, camcorder, projector, home theater, entertainment systems, security, and surveillance.



Color	S-Video 110 Punch-Down Catalog No.	S-Video F/F Coupler Catalog No.
Black	SFSV110BK	SFSVBK



Color	Almond	Black	Gray	Ivory	White
Catalog No.	SFBAL	SFBBK	SFBGY	SFBEI	SFBW

Audio Video Keystone Connectors

RCA Connectors

Distributes component and composite audio and video signals from device to device. Typical applications include TV, cable, VCR/DVD, camera, camcorder, projector, home theater, and entertainment centers.

Insulator Color	RCA Solder Coupler Termination			RCA Recessed Catalog No.
	RCA 110 Punch Down Black Housing Catalog No.	Office White Housing Catalog No.	Alternate Housing Color* Catalog No.	
Black	-	SFRC	SFRCBKXX	SFRCBKRX
Blue	SFRC110B	SFRCBOW	SFRCBXX	SFRCBRXX
Green	SFRC110GN	SFRCGNOW	SFRCGNXX	SFRCGNRX
Orange	-	SFRCOROW	SFRCORXX	SFRCORRX
Red	SFRC110R	SFRCR	SFRCRXX	SFRCRRXX
White	SFRC110W	SFRCW	SFRCWXX	SFRCWRXX
Yellow	SFRC110Y	SFRCY	SFRCYXX	SFRCYRX



Insulator Color	RCA Gold Pass-through, F/F Coupler	
	Office White Housing Catalog No.	Additional Housing Color* Catalog No.
Black	SFRCBKFF	SFRCBKFFXX
Blue	SFRCBFFOW	SFRCBFFXX
Green	SFRCGNFFOW	SFRCGNFFXX
Orange	SFRCORFFOW	SFRCORFFXX
Red	SFRCRFF	SFRCRFFXX
White	SFRCWFF	SFRCWFFXX
Yellow	SFRCYFF	SFRCYFFXX

* Additional Housing colors: **XX** = Almond = "AL"; Black = "BK"; Electric Ivory = "EI"; Gray = "GY"; Light Almond = "LA"; White = "W".

Gold Speaker Post Connectors and Plugs

Connectors	
Housing Color	Catalog No. Black Ring
Office White	SFSPGBK
	Catalog No. Red Ring
	SFSPGR



Plugs	
Housing Color	Catalog No. Black Plug
Office White	SPPBK10
	Catalog No. Red Plug
	SPPR10

1 bag = 10 connectors

Stereo Jacks

Use for distributing stereo or mono audio signals to and from devices.

Color	3.5mm Stereo Jack	1/4" Stereo Jack (Office White Only)
	Catalog No.	Catalog No.
Office White	SF35SJXX	SF14SJOW

Replace **XX** with color code: Black = "BK"; Electric Ivory = "EI"; Office White = "OW"; Telco Ivory = "TI"; White = "W".



Inline Keystone Coupler and Crossover Connectors, Category 5e

Use to deliver a quick and easy interconnect solution at the desktop or in the cross connect.

Catalog No.	Coupler T568A/B	Coupler T568A/B	Crossover
	Color: Black	Color: White	Gray Only
	SF5ECBK	SF5ECW	SF5ECOGY



USB 2.0 Connectors

Color	Format: A-to-A	Format: A-to-B
	Catalog No.	Catalog No.
Blue	SFUSBAAB	SFUSBABB
Office White	SFUSBAAOW	SFUSBABOW
White	SFUSBAAW	SFUSBABW



Blank Inserts

Color	Almond	Black	Gray	Ivory	Light Almond	White
Catalog No.	SFSBAL10	SFSBBK10	SFSBGY10	SFSBEI10	SFSBLA10	SFSBW10



Plates, Frames and Outlets

Multimedia Face Plates



Accepts AV and Voice/Data connectors. High impact resistant thermoplastic plate. UL Listed 1863 - Communication Circuit Accessory and CSA Certified.

Standard 1-Gang, 4.625" x 2.875"

Ports	1-port	2-port	3-port	4-port	6-port
See Color Code	NSP11XX	NSP12XX	NSP13XX	NSP14XX	NSP16XX

Standard 2-Gang, 4.625" x 2.875"

Ports	4-port	6-port
See Color Code	NSP24XX	NSP26XX

Midsize 1-Gang, 4.875" x 3.125"

Ports	1-port	2-port	3-port	4-port	6-port
See Color Code	NSP101XX	NSP102XX	NSP103XX	NSP104XX	NSP106XX

Colors - Replace **XX** with color code:

Almond = "**AL**"; Black = "**BK**"; Gray = "**GY**"; Ivory = "**I**"; Light Almond = "**LA**"; White = "**W**"

Decorator Face Plates



Description	Almond	Black	Brown	Gray	Ivory	Light Almond	White
1-Gang/1 Decorator	NP26AL	NP26BK	NP26	NP26GY	NP26I	NP26LA	NP26W
2-Gang/2 Decorator	NP262AL	NP262BK	NP262	NP262GY	NP262I	NP262LA	NP262W

Duplex Face Plates



Description	Almond	Black	Brown	Gray	Ivory	Light Almond	White
1-Gang/1 Duplex	NP8AL	NP8BK	NP8	NP8GY	NP8I	NP8LA	NP8W
2-Gang/2 Duplex	NP82AL	NP82BK	NP82	NP82GY	NP82I	NP82LA	NP82W

Decorator Frames



netSELECT™ Decorator Frames provide a stylized look for that finishing touch. Multimedia jacks insert into frame for custom configuration. Elongated strap for better wall box mounting.

Decorator Frame, 1-Gang

Ports	2-port	3-port	4-port	6-port
See Color Code	NS612XX	NS613XX	NS614XX	NS616XX

Decorator Frame, 1 Cat. 5e 110 Punch Down, 1 F-type Connector Coupler Bulkhead, Female to Female

Catalog No.

See Color Code **NS785XX**

Colors - Replace **XX** with color code:

Almond = "**AL**"; Black = "**BK**"; Gray = "**GY**"; Ivory = "**I**"; Light Almond = "**LA**"; White = "**W**"

Decorator Frame, 1-Gang Adapter .406" Dia. Hole

Color	Almond	Ivory	Light Almond	White
Catalog No.	NS621AL	NS621I	NS621LA	NS621W

Decorator Frame, 1-Gang Adapter Blank

Color	Almond	Ivory	Light Almond	White
Catalog No.	NS620AL	NS620I	NS620LA	NS620W

JLOAD™ Multimedia Outlet



Specifically designed to provide power, Cat. 5e and coax in a single gang box. For use in GVDI Fit box RU200 series. Includes decorator frame, voltage divider, one Cat 5e, one F-connector and one power receptacle 15A/125V, NEMA 5-15R.

Catalog No. **RJ650BK**

Telephone Wall Jacks



Designed for voice applications, these jacks provide an economical alternative to basic wall mount and performance needs.

Description	Catalog No.
Wall Phone Jack Quick Connect - 6-position, 4-conductor, (punch-down tool included)	NS721XX
Wall Phone Jack - 6-position, 4-conductor, screw terminations	NS722XX
Wall Phone Jack - 6-position, 6-conductor, screw terminations	NS725XX
Wall Phone Jack Quick Connect - 6-position, 4-conductor, Stainless Steel (punch-down tool included)	NS723SS
Wall Phone Jack - 6-position, 4-conductor, Stainless Steel, screw terminations	NS726SS

Colors - Replace **XX** with color code: Almond = "**AL**"; Ivory = "**I**"; White = "**W**"

Power Delivery

Decorator Duplex Receptacle Floor Box Kit - for Wood Floors

Includes steel box, flange and hinged door cover assembly with duplex receptacle. Designed for installation in wood floors, mounts to sub floor between joists.

Rating	Material	Catalog No.	Rating	Material	Catalog No.
15A/125V	Brass finish	RF515	NEMA 5-15R	Stainless finish	RF515SS

Flange and Hinged Door Cover Assembly

Includes duplex receptacle, neoprene gaskets, for use with steel box (RF500).

Rating	Material	Catalog No.	Rating	Material	Catalog No.
15A/125V	Brass finish	RF506	NEMA 5-15R	Stainless finish	RF506SS

Adjustable Floor Box, 2½" Deep

Three ½" knock-outs: One on bottom, one on each side, non-metallic sheathed cable clamps on each side.

Material: Steel	Catalog No. RF500
-----------------	--------------------------

Hinged Door Cover

Replacement door for RF515 and RF506 series.

Material	Catalog No.	Material	Catalog No.
Brass finish	RF507	Stainless finish	RF507SS



RF515



RF507

Floor Box Kit - for Concrete Floors

After the box has been secured in concrete, cut for height, apply PVC glue and push the cover assembly into the box. No fasteners or adjustment screws required.

PVC Floor Box with Concrete Protective Cover

Accepts ¾" and 1" schedule 40 and schedule 80 PVC conduit. Includes round box (4-7/8" dia. x 6" deep), four reducers, closure plugs, and concrete cover with locator flag.

Color: Gray	Catalog No. R400
-------------	-------------------------

Flange and Hinged Door Cover Assembly

Includes duplex receptacle, gasket, floor leveling PVC ring, high impact and chemically resistant nylon. Factory pre-assembled for easy drop-in installation.

Rating	Color	Catalog No.	Rating	Color	Catalog No.
15A/125V	Almond	RF406AL	NEMA 5-15R	Black	RF407BK

Low Voltage Divider

For use in PVC box RF400, when JLOAD™ multimedia outlet is used.

Color: Gray	Catalog No. RF408
-------------	--------------------------



RF400



RF407BK

Under Cabinet/Counter Power Distribution

netSELECT™ Under Cabinet/Counter boxes provide a convenient, out-of-sight way to distribute power and voice/data. These boxes comply with the NEC® for kitchen receptacles, with placement no more than 20" above the counter surface. They can also be placed under counter island, not lower than 15" from the surface.

Slim Fit Box

Offers the slimmest, sleekest, most stylish option for low-profile, out-of-sight mounting. Devices sold separately.

Color	Stainless Steel	White Metal	White Nylon*
Catalog No.	RU100SS	RU100W	RU170W

*Steel box with nylon cover.

GFCI Fit Box

Designed specifically for GFCI or JLOAD™ accommodation where internal wiring space is needed. Devices sold separately.

Color	Stainless Steel	White Metal	White Nylon*
Catalog No.	RU200SS	RU200W	RU270W

*Steel box with nylon cover.



RU100W



RU200W

Want to learn more?

Hubbell puts information at your fingertips.

www.hubbell-premise.com

For more information on Hubbell Premise Wiring's ten essential cabling infrastructure elements, our website offers:

- Online e-Catalog
- Product Spec Sheets
- Case Studies
- New Products
- Cabling Standards
- Press Releases
- Distributors
- Sales Contacts
- **MISSION CRITICAL®** Warranty
- Hub's Club

Download a copy of HPW's newest brochures or contact our customer service department to order our latest full line catalog.



Full Line Catalog

Features the latest technologies and innovations, including 10GbE connectivity, iFRAME server and column system, Audio/Video modules, and more.



Hubbell Educational Solutions for Power, Voice and Data

Hubbell Wiring Device-Kellems and Hubbell Premise Wiring are uniquely qualified to meet the challenges of educational institutions.



HI-IMPACT

Complete communication solution for harsh environments.

Access our website at **www.hubbell-premise.com**

or contact our Inside Sales Group for more information at **1-800-626-0005**.



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005

Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
Hubbell Canada Inc.
Hubbell Premise Wiring, Central America
Hubbell Premise Wiring, China
Hubbell Premise Wiring, Europe
Hubbell Premise Wiring, India
Hubbell Int'l. Inc., Korea Branch

852-2836-7131
905-839-1138
506-309-4158
86-21-6374 2660
44-01283 500500
91-99001-03341
(82 2) 2607 1363

Fax: 852-2836-7132
Fax: 905-839-9108
Fax: 506-260-1616
Fax: 86-21-6374 2799
Fax: 44-01283 500400
Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America
Hubbell de Mexico, S.A. de C.V.
Hubbell Premise Wiring, Middle East
Hubbell Premise Wiring, Puerto Rico
Hubbell-Taian Co., Ltd., Taiwan
Hubbell Premise Wiring, Venezuela

305-408-4501
(5255) 9151-9999
971-4-393-4192
787-855-1075
886-2-2522-1862
58-212-5156482

Fax: 305-408-8201
Fax: (5255) 9151-9989
Fax: 971-4-393-4194
Fax: 787-855-3265
Fax: 886-2-2522-1872
Fax: 58-212-6627258

B-NS1 4/07