



# S9446

15PAR38/LED/40'/3000K/120V/D  
 15 watt PAR38 LED; 3000K; 40' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable

### Compatible Dimmers

- Cooper TAL06P-C1
- LeGrand ADTP703TU
- Leviton 6674
- Lutron C.L. Family - Gen. 2.0 or above
- Lutron MACL-153M
- Lutron NTCL-250
- Lutron PD-6WCL
- Lutron SELV-300P



S9446

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9446	045923094460	120	15	90W	0.90	PAR38	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	15PAR38/LED/40'/3000K/120V/D	Dimmable	Silver	5-3/16"	4-3/4"	1200	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	40	12/6	Box	ENERGY STAR	Yes
Fixture Type	UL or ETL Listed	UL Classification	Warranty				
Enclosed Rated	Yes	cULus - Wet Location Rated	<a href="#">3 Year Limited</a>				



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

