



S9487

13PAR30/LN/LED/40'/2700K/90CRI
13 watt PAR30 Long Neck LED; 2700K; 25' beam spread;
Medium base; 120 volts

Features

- California T24 JA8-2016-E Qualified
- Reflector replacement lamp
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable



S9487

[Compatible dimmers for S9487](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9487	045923094873	120	13	50W	PAR30LN	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
13PAR30/LN/LED/40'/2700K/90CRI	Dimmable	Silver	4.6"	3-3/4"	820	25000	2700
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type
Warm White	90	40	12/6	Box	ENERGY STAR	Yes	Enclosed Rated
UL or ETL Listed	UL Classification	Warranty					
Yes	cULus - Wet Location Rated	3 Year Limited					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

