



# S9819

15.5A21/LED/27K/1600/120V/GU24  
 15.5 watt; A21 LED; Frosted; 2700K; GU24 base; 220' beam spread; 120 volts

### Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9819

[Compatible dimmers for S9819](#)

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	Lamp Code		
S9819	045923098192	120	15.5	0.96	A21	GU24	15.5A21/LED/27K/1600/120V/GU24		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Dimmable	Frosted	5-7/16"	2-5/8"	1600	25000	2700	Warm White		
CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed		
80	220	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR	Yes	Yes		
UL Classification						Warranty			
cULus - Damp Location Rated						<a href="#">3 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

