



NUVO 65-1082

4 Foot LED Ceiling Wrap Fixture



Fixture Type
Surface Mount LED

Collection
No

Style
Utility

Finish
White

Length
47.41"

Width
5.5"

Height
2.59"

Shade Description
Opaque

Shade Material
Acrylic

Number of Modules
1-Module

Light Source
LED Module

Lumen Output
3200 Lumens

Wattage
40 Watts

Lamp Type
LED

Bulb Type
LED Module

Bulb Base
Direct Wired

Bulb Included
Yes

Replaceable Light Source
No

Safety Rated
cETLus - Damp

Energy Saver
No

Energy Star
Yes

UPC
045923510823

Warranty
5-Year Warranty

Voltage
120-277 Volts

Average Rated Hours
50000

UL or ETL Listed
ETL Listed

Lamp Code
4FT LED CEILING WRAP

Kelvin Temp
4000K

CRI
90

Supplied Bulb
Linear LED Module

Dimmable/Non-Dimmable
Non-Dimmable