

Industrial Enclosures



SMALL - OIL, DUST & WATERTIGHT ENCLOSURES



Oil, Dust & Watertight EEMAC/NEMA 4/12

Features

- Oil & dust tight
- Watertight construction.
- Removable cover or piano hinged.
- All seam welded 14 ga. construction.
- Built to EEMAC/NEMA 4/12 requirements.
- Grey enamel finish.
- All complete with backplate.
- External wall mounting brackets.
- Neoprene gasketed.

Application

- For outdoor or indoor use.
- Suitable for electrical, control, or instrumentation housing.
- Completely weather resistant.
- For use in ship docks, construction sites, dairies, etc.
- Withstands water hose down.
- Suitable for terminal, transformer, or instrument or relay housing.
- Suitable as junction boxes or machinery wiring enclosures.

Also available in stainless steel and aluminum construction.

- All boxes available in stainless steel, 14 ga. type 304 construction - Suffix SSi.e. 4ST1084PHSS
- All boxes available in seam welded aluminum, utility grade 3/32" construction - Suffix AL, i.e. 4ST1084PHAL
- Also available are screw on cover enclosures - add prefix SOC, i.e. SOC4ST1084PH

CATALOGUE #	DIMENSIONS			PANEL SIZE
	H	W	D	
4ST443LOC	4"	4"	3"	NO PANEL
4ST443PH	4"	4"	3"	NO PANEL
4ST643LOC	6"	4"	3"	4.87" x 2.87"
4ST643PH	6"	4"	3"	4.87" x 2.87"
4ST644LOC	6"	4"	4"	4.87" x 2.87"
4ST644PH	6"	4"	4"	4.87" x 2.87"
4ST664LOC	6"	6"	4"	4.87" x 2.87"
4ST664PH	6"	6"	4"	4.87" x 2.87"
4ST864LOC	8"	6"	4"	6.87" x 4.87"
4ST864PH	8"	6"	4"	6.87" x 4.87"
4ST884LOC	8"	8"	4"	6.87" x 6.87"
4ST884PH	8"	8"	4"	6.87" x 6.87"
4ST1084LOC	10"	8"	4"	8.87" x 6.87"

CATALOGUE #	DIMENSIONS			PANEL SIZE
	H	W	D	
4ST1084PH	10"	8"	4"	8.87" x 6.87"
4ST1086LOC	10"	8"	6"	8.87" x 6.87"
4ST1086PH	10"	8"	6"	8.87" x 6.87"
4ST10104LOC	10"	10"	4"	8.87" x 8.87"
4ST10104PH	10"	10"	4"	8.87" x 8.87"
4ST12105LOC	12"	10"	5"	10.87" x 8.87"
4ST12105PH	12"	10"	5"	10.87" x 8.87"
4ST12126LOC	12"	12"	6"	10.87" x 10.87"
4ST12126PH	12"	12"	6"	10.87" x 10.87"
4ST14126LOC	14"	12"	6"	12.87" x 10.87"
4ST14126PH	14"	12"	6"	12.87" x 10.87"
4ST16146LOC	16"	14"	6"	14.87" x 12.87"
4ST16146PH	16"	14"	6"	14.87" x 12.87"