



S9280

3MR11/LED/25'/2700K/12V
3 watt; LED; MR11; 2700K; 25' beam spread; 25000 Average
rated Hours; 210 Lumens; GU4 base; 12 volts

Features

- Solid State LED Lighting
- High Efficiency
- Long Life
- UL approved for totally enclosed fixtures
- 20watt halogen MR11 equivalency

View [Transformer Compatibility](#)



S9280

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9280	045923092800	12	3	20W	0.61	MR11	GU4

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
GU4	3MR11/LED/25'/2700K/12V	Non-Dimmable	White	1-3/8"	1.38"	210	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	RoHS Compliant	UL or ETL Listed	Warranty
2700	Warm White	80	25	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

