





# S9830

5A19/OMNI/220/LED/27K  
5 watt; A19 LED; 2700K; Medium base; 220' beam spread; 120 volts

### Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- Approved for enclosed fixtures



S9830

[Compatible dimmers for S9830](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9830	045923098307	120	5	40W	0.86	A19	Medium

  

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	5A19/OMNI/220/LED/27K	Dimmable	Frosted	4-3/16"	2-3/8"	450	25000

  

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80	220	-20C (-4F) to a maximum of +45C (+113F)	24	Box	ENERGY STAR

  

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

