



# Clamps Aluminum

## Deadend Strain Clamps

### Features

Waved seat clamp for extra high holding power that exceeds requirements without damaging the cable. Conductor can be threaded through clamp without removing saddle. Lifting eye supplied on all sizes to facilitate hot line work. Hardware is galvanized steel; cotter pin is stainless steel.

Cat. No.	Type ASC-Aluminum				Dimensions in Inches					Ultimate Strength (Lb.)	
	Cable Range		Inches		A	B	C	D	E	Body	Eye
	Minimum	Maximum	Min	Max							
477SLA	No.6 STR.	- 3/0 STR. ALUM.	.18	.50	7 3/8	7/8	1	1 1/4	1/2	8000	4000
62SLA	No.2 STR.	- 300 MCM STR.	.30	.63	8 15/16	7/8	1	1 3/8	1/2	9000	5000
93SLA	3/0 STR.	- 556.5 MCM STR.	.46	.93	9 5/8	7/8	1	1 3/8	1/2	9000	5000
156ASC	477 MCM STR.	- 1800 MCM STR.	.79	1.56	14	7/8	1	1 3/8	5/8	12000	8000

## Type MSC-Iron Hot Dip Galvanized

Available upon request.



477SLA



93SLA

