



S9769

75W/LED/HID/MB/5000K/100-277V
 75 watt - LED HID Replacement; 5000K; Mogul Extended base;
 Adjustable beam angle; 100-277 volts

Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 year limited warranty



S9769

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Width (360°)	Width (270°)	Width (180°)
4.2"	9.3"	10.9"

Item Number	Product Line	UPC	Input Voltage	Watts	Base	ANSI Base	Lamp Code
S9769	Hi-Pro	045923097690	100 - 277	75	Mogul Extended	EX39	75W/LED/HID/MB/5000K/100-277V

Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Non-Dimmable	White	8-5/8"	4-3/16" (Open 10-7/8")	9800	50000	5000	Natural Light

CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification
80+	Adjustable: 360; 270; 180	12	Box	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated

Warranty

[5 Year Limited](#)



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

