



# S9411

13PAR30/SN/LED/25/3000K/120V/D  
 13 watt PAR30 Short Neck LED; 3000K; 25° beam spread;  
 Medium base; 120 volts

## Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9411

[Compatible dimmers for S9411](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base	
S9411	045923094118	120	13	50	PAR30SN	Medium	E26	
Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
13PAR30/SN/LED/25/3000K/120V/D		Dimmable	Silver	3-5/8"	3-3/4"	1000	25000	3000
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type	
Warm White	80	25	12/6	Box	ENERGY STAR	Yes	Enclosed Rated	
UL or ETL Listed		UL Classification			Warranty			
Yes		cULus - Wet Location Rated			<a href="#">3 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

