



# S9590

6A19/LED/2700K/120V  
6 watt; A19 LED; Frosted; 2700K Medium base; 220' beam spread; 120 volts; Non-Dimmable

### Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable
- Approved for enclosed fixtures



S9590

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9590	045923095900	120	6	40W	0.61	A19	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	6A19/LED/2700K/120V	Non-Dimmable	Frosted	4-5/16"	2.38"	480	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80	220	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR

RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Yes	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

