

# CTS Series

## 20 AMP - 600 VOLTS Transformer Rated



CATALOGUE #	DESCRIPTION	WEIGHT
<b>CTS409PW</b>	5 Jaw with circuit closing left side for "CMS" applications*	5 lbs.
<b>CTS459PW</b>	5 Jaw with circuit closing left side for 4 Jaw application**	5 lbs.
<b>CTS408PW</b>	4 Jaw with circuit closing on left and right side	5 lbs.
<b>CTS429PW</b>	4 Jaw with circuit closing on left and right side	5 lbs.

- Transformer rated for services over 200 Amps
- CSA approved for copper only
- CSA enclosure 3
- Range No. 14 - No. 8 CU
- Circuit closing feature to short out current transformer upon removal of meter
- Pole mountable
- Central metering systems

\*5th Jaw in 9 O'clock position, meets 2004 Hydro One code  
 \*\*5th Jaw in 6 O'clock position, Dummy Jaw in lower right hand position For use on 4 Jaw CMS applications

KNOCKOUT CODE	CONDUIT SIZE
<b>C</b>	1", 1 1/4", 1 1/2"
<b>A</b>	1/2", 1", 1 1/4"
<b>B</b>	1", 1 1/4"



**CTS409PW  
CTS459PW**

