



S9802

15A21/LED/2700K/120V/4PK
15 watt; A21 LED; 2700K; Medium base; 240' beam spread;
120 volts; 4-pack

Features

- A-Shaped replacement lamp
- 100w equivalent
- Approved for enclosed fixtures
- Damp location rated



4 Pack

S9802

Item Number	UPC	Input Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9802	045923098024	120	15	100W	0.90	A21	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	15A21/LED/2700K/120V/4PK	Non-Dimmable	Frost	5-1/4"	2-3/8"	1500	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant
2700	Warm White	80	240	-20C (-4F) to a maximum of +45C (+113F)	4	4Pk	Yes

Fixture Type	UL or ETL Listed	UL Classification	Warranty
Enclosed Rated	Yes	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

