



S9393

45W/LED/HID/5000K/100-277V/EX39
 45 watt - LED HID Replacement; 5000K; Mogul extended base;
 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Qualified
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum lamp compartment dimensions:

235mm x 235mm x 440mm (9.25" x 9.25" x 17.3")

Optional accessory: In-line surge protector [80-929](#)



S9393

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent	
S9393	Hi-Pro	045923093937	100 - 277	45	300W	65W	175W	
Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Mogul Extended	EX39	45W/LED/HID/5000K/100-277V/EX39		Non-Dimmable	White	10-3/4"	3.69"	6000

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)	12	Box
DLC ID:		RoHS Compliant	UL or ETL Listed	UL Classification	Warranty		
Search under: S9393A or P3WZ3974 or PTX83RBS DLC Search		Yes	Yes	cULus - Damp Location Rated	5 Year Limited		



<p>National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com</p>	<p>Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico</p>	<p>Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027</p>	
--	--	---	---