



S9751

40W/LED/HID/MB/5000K/100-277V
 40 watt - LED HID Replacement; 5000K; Mogul extended base;
 100-277 volts

Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 year limited warranty

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Width (360°)	Width (270°)	Width (180°)
3.5"	7.7"	8.9"

Minimum lamp compartment dimensions: 235mm x 235mm x 210mm (9.25" x 9.25" x 8.27")



S9751

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9751	Hi-Pro	045923097515	100 - 277	40	300W	65W	175W

Power Factor	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
0.90	Mogul Extended	EX39	40W/LED/HID/MB/5000K/100-277V	Non-Dimmable	White	7-7/8"	3-1/2" (Open 8-7/8")

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack
----------------	---------------------	-------------	-------	-----	-----------------	-----------------------	------

5200	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	-20C (-4F) to a maximum of +65C (+149F)	12/6
Package Type	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty		
Box	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	5 Year Limited		



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

