



# S9599

12W/LED/5-6"TRIM/2700K/120V/2P  
12 watt; Downlight Retrofit LED; 5"-6" Trim; 2700K; Medium base; 120 volts; 110 deg. beam spread; 2-pack

### Features

- Solid State LED lighting
- Downlight Retrofit
- Long life
- Dimmable
- Adjustable length: 4-1/2" - 6-5/16"
- Fits 5" - 6" recessed cans



S9599

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Fixture Type	Base
S9599	045923095993	120	12	65W	Down Light	Retrofit	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	12W/LED/5-6"TRIM/2700K/120V/2P	Dimmable	White	6 3/8"	7 1/2"	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed
2700	Warm White	80+	110	12/2	Box	Yes	Yes
UL Classification						Warranty	
cULus Classified - Damp Location Rated						<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

