



S9598

8.5W/LED/4"TRIM/2700K/120V/2PK
8.5 watt; Downlight Retrofit LED; 4" Trim; 2700K; Medium base;
120 volts; 2-pack

Features

- Solid State LED lighting
- Downlight Retrofit
- Long life
- Dimmable
- Adjustable length: 3-13/16" - 5-3/8"
- Fits 4" recessed cans



S9598

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Fixture Type	Base
S9598	045923095986	120	8.5	45W	Down Light	Retrofit	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	8.5W/LED/4"TRIM/2700K/120V/2PK	Dimmable	White	5 3/8"	5 1/8"	500	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed
2700	Warm White	80+	115	12/2	Box	Yes	Yes
UL Classification						Warranty	
cULus Classified - Damp Location Rated						3 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

