



S9752

60W/LED/HID/MB/5000K/100-277V
 60 watt - LED HID Replacement; 5000K; Mogul extended base;
 100-277 volts

Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay or low bay
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 year limited warranty



S9752

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent	
S9752	Hi-Pro	045923097522	100 - 277	60	500W	85W	250W	
Power Factor	Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
0.90	Mogul Extended	EX39	60W/LED/HID/MB/5000K/100-277V		Non-Dimmable	White	8 9/16"	4 1/4"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	
7800	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	12/6	Box	
RoHS Compliant		Fixture Type	UL or ETL Listed		UL Classification		Warranty	
Yes		Enclosed Rated	Yes		cULus - Damp Location Rated		5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

