

Mogul Extended	EX39	120W/LED/HID/5000K/100-277V/EX39			Non-Dimmable	White	10-3/8"	5.87"	16000
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type	
50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)		4	Box	
DLC ID:		RoHS Compliant		UL or ETL Listed	UL Classification		Warranty		
Search under: S9397A or PNT1PM7G or PXF3ZPKD DLC Search		Yes		Yes	cULus - Damp Location Rated		5 Year Limited		



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051