



S9433

13PAR30/LN/LED/40'/4000K/120V/D
 13 watt PAR30 Long Neck LED; 4000K; 40' beam spread;
 Medium base; 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9433

[Compatible dimmers for S9433](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9433	045923094330	120	13	75W	PAR30LN	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
13PAR30/LN/LED/40'/4000K/120V/D	Dimmable	Silver	4.6"	3-3/4"	1000	25000	4000

Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type
Cool White	80	40	12/6	Box	ENERGY STAR	Yes	Enclosed Rated

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Wet Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

