



S9595

9.5A19/LED/5000K/120V
9.5 watt; A19 LED; Frosted; 5000K Medium base; 220' beam spread; 120 volts; Non-Dimmable

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable
- Approved for enclosed fixtures



S9595

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9595	045923095955	120	9.5	60W	0.60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	9.5A19/LED/5000K/120V	Non-Dimmable	Frosted	4-5/16"	2.38"	800	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
5000	Natural Light	80	220	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR
RoHS Compliant	UL or ETL Listed	UL Classification	Warranty				
Yes	Yes	cULus - Damp Location Rated	3 Year Limited				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

