



S9816

15.5A21/LED/3000K/1600L/120V/D
 15.5 watt; A21 LED; Frosted; 3000K; Medium base; 220' beam spread; 120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9816

[Compatible dimmers for S9816](#)

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	ANSI Base
S9816	045923098161	120	15.5	0.96	A21	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15.5A21/LED/3000K/1600L/120V/D	Dimmable	Frosted	5-9/16"	2-5/8"	1600	25000	3000
Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR	RoHS Compliant
Soft White	80	220	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR	Yes
UL or ETL Listed	UL Classification	Warranty					
Yes	cULus - Damp Location Rated	3 Year Limited					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

