



S9710

25T5/LED/46-840/DR
 25 watt T5 LED; Miniature bi-pin base; 4000K; 50000 average rated hours; 3200 lumens



Features

- Direct Replacement - for use on Electronic Instant Start and Rapid Start ballasts with no rewiring required*
- Ballast required
- Solid State LED lighting
- High efficacy
- Long life
- 54watt Fluorescent equivalency
- Approved for enclosed luminaires
- 5 year Limited warranty

S9710

*May not be compatible with all instant start ballasts.

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base	Lamp Code
S9710	045923097102	25	54W	T5	Miniature Bi Pin	G5	25T5/LED/46-840/DR
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Non-Dimmable	White	48"	0.625"	3200	50000	4000	Cool White
CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
82	185	-20°C (-4°F) to a maximum of +45°C (113°F)	10	Box	Yes	Yes	cULus - Damp Location Rated
Warranty							
5 Year Limited							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

