



S9488

15PAR38/LN/LED/40'/2700K/90CRI
15 watt; PAR38 LED; 2700K; 40' beam spread; Medium base;
120 volts

Features

- California T24 JA8-2016-E Qualified
- Reflector replacement lamp
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable



S9488

[Compatible dimmers for S9488](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base	
S9488	045923094880	120	15	90W	PAR38	Medium	E26	
Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15PAR38/LN/LED/40'/2700K/90CRI		Dimmable	Silver	5-3/16"	4-3/4"	1000	25000	2700
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type	
Warm White	90	40	12/6	Box	ENERGY STAR	Yes	Enclosed Rated	
UL or ETL Listed		UL Classification				Warranty		
Yes		cULus - Wet Location Rated				3 Year Limited		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

