



S9839

9.5A19/OMNI/220/LED/50K
9.5 watt; A19 LED; 5000K; Medium base; 220° beam spread;
120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- Approved for enclosed fixtures



S9839

[Compatible dimmers for S9839](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9839	045923098390	120	9.5	60W	0.88	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	9.5A19/OMNI/220/LED/50K	Dimmable	Frosted	4-1/2"	2.38"	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
5000	Natural Light	80	220	-20C (-4F) to a maximum of +45C (+113F)	24	Box	ENERGY STAR
RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty			
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	3 Year Limited			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

