



# S9911

25T5/LED/46-850/DR  
 25 watt T5 LED; Miniature bi-pin base; 5000K; 50000 average rated hours; 3500 lumens



### Features

- Direct Replacement - for use on Electronic ballasts with no rewiring required\*
- Replaces F54T5/HO linear fluorescent lamps
- High efficacy
- Long life
- 25watt - 32watt Fluorescent equivalency
- Approved for enclosed luminaires
- DLC Qualified
- 5 year Limited warranty

S9911

\*May not be compatible with all rapid start ballasts.

Ballast required

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable
S9911	045923099113	25	T5	Miniature Bi Pin	G5	25T5/LED/46-850/DR	Non-Dimmable
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	48"	0-5/8"	3500	50000	5000	Natural Light	82
Beam Spread Deg	Pack	DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
185	10	PANAEZ2Y; PRVRXZXF <a href="#">DLC Search</a>	Yes	Yes	cULus Classified - Damp Location Rated	<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

