



Bolts

THIMBLE & OVAL EYE BOLTS

Thimble Eye Bolts

Complete with square nuts. Hot dip galvanized, cone points. C.S.A. Drawing No. B-7 & B-5

Cat. No.	D	L	T	Std. Pkg.	Wt.-lbs./ C
Straight					
858TE	5/8	8	6	25	125
1058TE	5/8	10	6	25	144
1258TE	5/8	12	6	25	162
1458TE	5/8	14	6	25	198
Bent Thimble Eye Bolts					
1058BTE	5/8	10	6	25	144
1258BTE	5/8	12	6	25	162
1458BTE	5/8	14	6	25	198
1010BTE	1	10	6	10	190



1058TE



1058BTE

Oval Eye Bolts

Hot dip galvanized Bolts 6" and longer have cone points.

Eye Dimensions (A x B) for 1/2" bolt: 1 x 1-1/2; for 5/8 and 3/4" bolts: 1-1/2 x 2

Cat.No.	Diameter	L	T	Std.Pkg.	Wt.-lbs./ C
6580E	5/8	6	3	50	122
8580E	5/8	8	4	50	136
10580E	5/8	10	4	25	150
12580E	5/8	12	6	25	168
14580E	5/8	14	6	25	186
16580E	5/8	16	6	25	204
18580E	5/8	18	6	25	222
20580E	5/8	20	6	25	250
22580E	5/8	22	6	25	270
24580E	5/8	24	6	25	290
10340E	3/4	10	6	25	225
12340E	3/4	12	6	25	250
14340E	3/4	14	6	25	275
16340E	3/4	16	6	25	295
18340E	3/4	18	6	25	320

Other sizes available upon request.



10580E