



Racks

SECONDARY RACKS

Secondary Racks-Heavy Duty

Knob Type Racks:

Complete with knob type insulators and non-extended ends.

C.S.A. Specification C-83, Drawing No. R-17 wire spacing 8".

Cat.No.	No. of wires	Overall Length	Std.Pkg.	Wt.-lbs./ C
1045R	1	4 1/2	10	250
2145R	2	14 1/2	5	600
3200R	3	20 1/2	5	850
4280R	4	28"	5	1100
5360R	5	36"	5	1350
2180TSR	2	19"	5	500

Add 13 at the end of part number when 13/16 mounting holes are required.
Insulator used on above racks #1085D.



Cat.No.	Width	Height	Hole	Pkg. Qty.	Wt.-lbs./ C	
Knob-Type (U-Bolt) Insulator only:						
1085D	3	3-3/4	1	25	170	For knob type rack. U-bolts not included.



1085D

Medium Duty Racks

- 11/16 mounting holes.

- complete with Insulators (1606WSP).

Cat.No.	No. of Wires	Overall Length	Width	Spacing	Std. Pkg.	Wt.-lbs./ C
1172E	2	15 1/2	2 5/8	8	5	420
1173E	3	23 1/2	2 5/8	8	5	690
1174E	4	31 1/2	2 5/8	8	5	960

Clevis size - 2 5/16 high x 1 3/4 wide.

