

JA Series



METER
SOCKETS

200 AMP SOCKET c/w Breaker

CATALOGUE #	DESCRIPTION	ENCLOSURE SIZE H X W X D	WEIGHT
JA402P	c/w 200 Amp breaker, 4 jaw, 120/240 VOLTS, single phase, 3 wire	30" x 10 ¹ / ₄ " x 5 ¹ / ₄ "	25 lbs.
JA402PSD-LB	as above, less breaker (will accomodate square D breaker only)	30" x 10 ¹ / ₄ " x 5 ¹ / ₄ "	24 lbs.
JA402PSD	c/w 200 amp square D breaker	30" x 10 ¹ / ₄ " x 5 ¹ / ₄ "	25 lbs.

- 200 Amp - 120/240 VOLT
- Combination meter socket & circuit breaker
- CSA enclosure 3
- Conductor range #6 - 250 MCM CU/AL
- Suitable for temporary service, farm service, trailers, recreational parks, commercial and residential locations.
- Service entrance rated

- Also available with 125 Amp breaker or 150 Amp breaker upon request
- Also available less breaker

KNOCKOUT CODE	CONDUIT SIZE
G	1 ¹ / ₄ ", 1 ¹ / ₂ ", 2", 2 ¹ / ₂ "

