

CTS Series

20 AMP - 600 VOLTS c/w Test Switch Comp.



CATALOGUE #	DESCRIPTION	WEIGHT
CTS400PW	4 Jaw	24 lbs.
CTS500PW	5 Jaw - 5th Jaw in 6 O'clock position	24 lbs.
CTS405PW	5 Jaw - for 4th Jaw application*, 5th Jaw at 9 O'Clock position	24 lbs.
CTS800PW	8 Jaw	26 lbs.
CTS130PW	13 Jaw	26 lbs.
CTS139PW	13 JAW - with by-pass	26 lbs.
CTS130PW-TS	13 JAW c/w 10 pole test switch	30 lbs.
CTS400PW-TS	4 JAW -c/w 4 pole test switch	30 lbs.

- Transformer rated for services over 200 Amps
- CSA enclosure 3
- CSA approved for copper only
- Conductor range for No. 14 - No. 8 CU
- Meter socket with compartment for test switches or test blocks
- Bottom cover is lockable and sealable

KNOCKOUT CODE	CONDUIT SIZE
N	3/4", 1", 1 1/4"

