

AV In-Wall Enclosure

15A, 125V, 2-Gang

Recessed TR Duplex Receptacle with Cable Pass Thru

HUBBELL

Features

- Tamper-Resistant (TR) duplex
- Easily mounts to box
- Cable pass thru organizes and protects low voltage cables

Ordering Information

Description	Device Color	UPC	Catalog Number
Smooth face, back and side wired.	White	88377830583	RR1512W

Listings

UL Listed to UL 498
CSA Certified 22.2, No. 42

Specifications

Pass Thru Brushes	Nylon
Face	Nylon
Base	PVC
Power Contacts	.030 in. (.8mm) Brass
Ground Contacts	.014 in. (.35mm) Brass
Terminal Screws	Plated Steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc Plated Steel

Performance

Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-12 AWG stranded or solid copper conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Gangable AV Wall Box	HBL985
Recessed TR AV Plastic Box	RR1500

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

