

ES1150

2" ELEC SPLICE KT W BOOT ENCLS

UPC: 085937079510

Country of Origin:

UNSPSC: 39121718

USA

Commodity: Cable splicing kits



"SHAKE N SEAL" electrical splice kits offer absolute protection for any splice (up to 600V) in a wet or damp environment.

Product Attributes

Brand Name	Minerallac Company
Sub Brand	Uruseal [®]
Type	Shake N' Seal [®] Electrical Splice Kit
Special Features	2" Permanent Splice Protection with Boot Enclosure
Application	Single Service Conductors, Through Splice, Direct Burial, Water Tight
Standard	CSA [®] LR204840, UL [®] 31YB
Cable Type	Recommended Single-Conductor Wire
Number Of Cables	8AWG-4, 6AWG-3, 4AWG-2, 3AWG-2, 2AWG-2, 1AWG-2, 1/0AWG-2, 2/0AWG-2, 3/0AWG-2, 4/0AWG-2
Cable Size	18-4/0 AWG
Voltage Rating	600 Volts or Less
Color	Gray
Insulation	Permanent Encapsulant
Operating Temperature	Max 90° C

Item Status: Active
Standard Qty: 1

Minerallac Company

Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com